

DU 1150 RV

Drying unit, with ventilation slots, electric

For 1150 mm-wide appliances and optimal internal and external drying of items.

EAN: 4002516265184 / Material number: 11382350 / Old Material Number: 69250007USA



- With top-box panelling; air supply via the room.
- Includes 2 H14 HEPA filters
- Maximum safety – HEPA filter directly in front of wash cabinet
- Air flow rate 250 m³/h
- HEPA filter service life: 1,000 hours

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PLW 8617	•
Dimensions and weight	
External dimensions, net height in mm	855
External dimensions, net width in mm	850
External dimensions, net depth in mm	1190
External dimensions, gross height in mm	39 7/8 (1010)
External dimensions, gross width in mm	33 1/2 (850)
External dimensions, gross depth in in (mm)	47 1/4 (1200)
Net weight in kg	265 (120.00)
Gross weight in kg	303 (137.00)