

PR 900  
 Built-in report printer  
 For printing process protocols.



- Thermal printer with 60 mm paper width
- Can be installed on the outfeed side with 2-door models

EAN: 4002516362081 / Material number: 11491220 / Old Material Number: 69247004D

<b>Product category</b>	
Large-capacity washer-disinfectors, laboratory	•
<b>Machine affiliation</b>	
PLW 8615	•
PLW 8616	•
<b>Product characteristics</b>	
Colour	Black
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0.00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	37 7/16 (950) in (mm)
External dimensions, net width in mm	3 1/16 (77) in (mm)
External dimensions, net depth in mm	2 3/4 (69) in (mm)
External dimensions, gross height in mm	4 15/16 (125)
External dimensions, gross width in mm	7 7/8 (200)
External dimensions, gross depth in in (mm)	39 3/8 (1000)
Net weight in kg	7 (2.87)
Gross weight in kg	8 (3.59)