

## DOS K 85 flex

Dispenser module for 5-10 litre canisters

for the automatic dispensing of liquid media, with level indicator.



- Dispenser monitoring – high process security as per EN ISO 15883
- For dispensing liquid cleaning agent/neutralizing agent
- 13 7/8 (352) in (mm) mm suction lance for 5–10 l canisters with flexible cap
- Conversion kit for suction lance for 10–30 l canisters available

EAN: 4002516365280 / Material number: 11498910 / Old Material Number: 69747052USA

|   |              |
|---|--------------|
| <b>Product category</b>                     |              |
| Glassware Washers, laboratory               | •            |
| Thermal disinfectors                        | •            |
| Washer-disinfectors, medical                | •            |
| <b>Machine affiliation</b>                  |              |
| PG 8581                                     | •            |
| PG 8562                                     | •            |
| PG 8582                                     | •            |
| PG 8583                                     | •            |
| PG 8591                                     | •            |
| PG 8592                                     | •            |
| PG 8593                                     | •            |
| <b>Product category</b>                     |              |
| Dispenser system                            | •            |
| <b>Product characteristics</b>              |              |
| Production rate in ml/60 s                  | 55           |
| Length of suction lance in mm               | 13 7/8 (352) |
| <b>Standard electrical connection</b>       |              |
| Number of phases                            | 1            |
| Neutral conductor                           | N            |
| AC / DC                                     | AC           |
| Voltage in V                                | 200-240      |
| Frequency in Hz                             | 60           |
| Total rated load in kW                      | 0.01         |
| Fuse rating in A                            | 0            |
| <b>Dimensions and weight</b>                |              |
| External dimensions, net height in mm       | 0            |
| External dimensions, net width in mm        | 0            |
| External dimensions, net depth in mm        | 0            |
| External dimensions, gross height in mm     | 6 3/8 (160)  |
| External dimensions, gross width in mm      | 7 7/8 (198)  |
| External dimensions, gross depth in in (mm) | 18 7/8 (478) |
| Net weight in kg                            | 5 (2.21)     |
| Gross weight in kg                          | 6 (2.43)     |
| <b>Standards / certs / symbols</b>          |              |
| CE  | •            |