

PFD 101 U

Built-under dishwasher, ADA compliant

for large loads of dishes in households and commercial settings.



- Wash performance: 13 place settings in just 28 min^{*}
- 13% less energy consumption^{**}
- Everything completely dry – AutoOpen assisted drying
- Intuitive to operate thanks to clear fascia panel design
- Flexible loading of wash items for the best cleaning results

^{*} Depending on site conditions (temperature of incoming water / power connection) values given may vary.

^{**} Based on the ECO program, compared to the predecessor model.

EAN: 4002516366850 / Material number: 11605420 / Old Material Number: 61010102USA

Construction type and design	
Construction type	Built-under dishwasher
Product line	ProfilLine
Wash system	Fresh water dishwasher
Number of wash levels	2
Front	Stainless steel
Side panels	Galvanised
Control panel colour	CleanTouch Steel
Application	
Suitable for retirement and care homes	•
Suitable for hospitals	•
Suitable for guesthouses	•
Suitable for kindergartens	•
Suitable for universities and schools	•
Suitable for offices	•
Suitable for domestic use	•
Suitable for small businesses	•
Suitable for sports clubs	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Circulation pump, Qmax in gal/min (l/min.)	19.8 (75)
Shortest program duration in minutes	52
Maximum final rinse temperature in °F (°C)	180 (82)
Cleaning performance, place settings/cycle	13
Service life in wash cycles	12500
Miele MOVE	
Network-enabled with Miele MOVE (not available in Canada)	•
Controls	
Control type	Electronic controls
Program selection	Program selectors
Max. delay start in h	24
Time left display	•
Programs [quantity]	8
Program sequence indicator	•
Choice of display language	•
Check filter indicator	•
Standard electrical connection	
Electrical connection	AC 120V 60HZ
Heater rating in kW	1.30
Total rated load in kW	1.40
Fuse rating in A	15
Length of power cord in ft. (m)	5 (1.70)
NEMA plug: 5-15	•
Possible voltage variant 1	
Electrical connection	2N AC 120/208-240V, 60HZ
Heater rating in kW	3.50-3.80
Total rated load in kW	3.70-4.00

PFD 101 U

Built-under dishwasher, ADA compliant

for large loads of dishes in households and commercial settings.



EAN: 4002516366850 / Material number: 11605420 / Old Material Number: 61010102USA

Fuse rating in A	30
Water connection/drainage	
Cold or hot water [number]	1
Required flow pressure in bar	1.00-10.00
Drain pump [DN]	22
Maximum drain pump height (delivery head) in in. (cm)	39 3/8 (100)
Integrated water softener	•
Maximum water hardness in (mmol/l)	38.02 (6.50)
Water protection system	Waterproof system
Length of water inlet hose in in. (cm)	59 1/8 (150)
Length of water drain hose in in. (cm)	59 1/8 (150)
Dimensions and weight	
External dimensions, height in in. (mm)	31 3/4 (805)
External dimensions, width in in. (mm)	23 9/16 (598)
External dimensions, depth in in (mm)	22 1/2 (570)
External dimensions, gross height in in. (mm)	37 13/16 (960)
External dimensions, gross width in in. (mm)	26 7/16 (670)
External dimensions, gross depth in in (mm)	27 9/16 (700)
Usable space in wash cabinet, height in in. (mm)	21 5/16 (540)
Usable space in wash cabinet, width in in. (mm)	20 1/8 (510)
Usable space in wash cabinet, depth of upper basket in in. (mm)	17 3/4 (450)
Usable space in wash cabinet, depth of lower basket in in. (mm)	17 3/4 (450)
Rack height above floor in in. (mm)	8 5/16 (210)
Required niche width in in. (mm)	23 5/8 (600)
Net weight lb [kg]	98 (44)
Gross weight in lb (kg)	113 (51)
Maximum floor load in N/m ²	1000
Emission values	
Emission sound pressure level at workplace (LpA)	33 dB(A) re 20 µPa
Sound power level LwA	0.0
Programs	
Universal	•
Short	•
SaniWash	•
Cold / pre-wash	•
Glasses	•
Plastics	•
Energy save / Economy	•
Intensive	•
Basket design	
ExtraComfort P baskets	•
Flexible FlexLine Baskets	•
FlexCare glass holder [number]	2
FlexCare cup rack [number]	1
Cutlery basket	•
Height-adjustable upper basket	•
Features	
Commercial-grade electrical connection	•

PFD 101 U

Built-under dishwasher, ADA compliant

for large loads of dishes in households and commercial settings.



EAN: 4002516366850 / Material number: 11605420 / Old Material Number: 61010102USA

Drying	AutoOpen assisted drying, Active condensation drying, Extra drying
1 combi dispensing unit in the door for powder cleaning agent and rinsing agent	•
Wash cabinet made of high-quality stainless steel	•
EcoFeedback	•
Brilliant GlassCare	•
Child lock	•
Adjustable final rinse temperature	•
Optical interface	•
SmartStart	•
FlexiTimer with EcoStart	•
Wi-Fi module	•
Standards / certs / symbols	
CE	•
Complies with Machinery Directive 2006/42/EC	•
VDE	•
EMC radio suppressed	•
DIN EN 17735	•
EN 1717	•
UL	•