

## PWM 912 [EH DV DD]

Professional washing machine, external heating  
with detergent drawer, M Touch Pro Plus – freely programmable.



- Drum volume 3.88 (110) ft<sup>3</sup> (l), load size 25 (11.0) lb (kg)
- Top cleaning & consumption values – innovative Miele technology
- Ideal operation thanks to touch colour display – M Touch Pro Plus
- Simple and safe operation thanks to automatic door lock
- Connected for the future using LAN and Wi-Fi

EAN: 4002516444701 / Material number: 11803080 / Old Material Number: 51912059NAM

| Construction type and design  |                                |
|---|--------------------------------|
| Construction type   | Front loader                   |
| Product line  | Performance Plus               |
| Front   | Stainless steel                |
| Control panel colour  | Stainless steel                |
| Maximum load with a load ratio of 1:9 in lbs (kg)                             | 27 (12.0)                      |
| Load ratio  | 1:9                            |
| Load in lbs. (kg)   | 25 (11.0)                      |
| Drum volume in l  | 3.88 (110) ft <sup>3</sup> (l) |
| Door opening [Ø] in in. (mm)  | 16 3/8 (415)                   |
| Door-opening angle in degrees   | 180                            |
| Door hinging  | right                          |
| Automatic door lock   | •                              |
| Innovative suds container   | •                              |
| Maintenance-free motor with frequency converter                               | •                              |
| Patented honeycomb drum 2.0   | •                              |
| Application   |                                |
| Suitable for hotels and restaurants   | •                              |
| Suitable for retirement and care homes  | •                              |
| Suitable for facility management  | •                              |
| Suitable for dry cleaners   | •                              |
| Suitable for commercial laundromats   | •                              |
| Suitable for small businesses   | •                              |
| Suitable for fire departments and rescue services                             | •                              |
| Suitable for stud farms and stables   | •                              |
| Suitable for universities, schools, and kindergartens                         | •                              |
| Suitable for hospitals  | •                              |
| Suitable for camp sites   | •                              |
| Suitable for sports clubs   | •                              |
| Suitable for beauty salons, spas, and fitness centres                         | •                              |
| Suitable for the petrochemical industry                                       | •                              |
| Suitable for amusement parks and holiday resorts                              | •                              |
| Suitable for public / community facilities                                    | •                              |
| Performance data  |                                |
| Tested virucidal efficacy   | •                              |
| Proven hygiene  | •                              |
| Specific water consumption for hot water connection in l/kg                   | 5.90                           |
| Specific energy consumption for hot water connection in kWh/kg                | 0.02                           |
| Water consumption with hot water connection in l                              | 70.8                           |
| Water consumption for hot water connection in Mops standard 60°C program in l | 133.6                          |
| Energy consumption with hot water connection in kWh                           | 0.27                           |
| Program duration with hot water connection in minutes                         | 42                             |
| Water consumption in Economy program with hot water connection in l           | 68.4                           |
| Energy consumption in Economy program with hot water connection in kWh        | 0.19                           |
| Program duration with hot water connection in Economy program in minutes      | 31                             |

## PWM 912 [EH DV DD]

Professional washing machine, external heating  
with detergent drawer, M Touch Pro Plus – freely programmable.



EAN: 4002516444701 / Material number: 11803080 / Old Material Number: 51912059NAM

|  |                             |
|--|-----------------------------|
| Program cycle time in minutes for Mops standard 60°C program with hot water connection | 43                          |
| Residual moisture with cold rinse in %   | 48                          |
| Residual moisture with hot rinse in %  | 44                          |
| Residual moisture when reprocessing wiping cloths in %                                 | 25                          |
| Spin speed in rpm  | 1150                        |
| g-factor   | 458                         |
| Tested operating hours   | 30000                       |
| <b>Controls</b>  |                             |
| Control type   | M Touch Pro Plus            |
| Programmability  | Freely programmable         |
| Max. delay start in h  | Can be selected freely      |
| Time left display  | •                           |
| Program sequence indicator   | •                           |
| Choice of display language   | •                           |
| Option to enter weight prior to start of program                                       | •                           |
| <b>Standard / target grp programs</b>  |                             |
| Basic programs   | •                           |
| <b>Dispensing</b>  |                             |
| Detergent drawer   | 3 compartments              |
| Maximum number of connections for liquid dispenser pumps [number]                      | 12                          |
| Empty sensing  | •                           |
| <b>Standard electrical connection</b>  |                             |
| Heating type   | External heating            |
| Electrical connection  | 240V 60HZ 1 PH 3 WIRE       |
| Total rated load in kW   | 2.30                        |
| Fuse rating in A   | 20                          |
| <b>Water connection/drainage</b>   |                             |
| Cold water [number]  | 3 x 1/2" hose w/ 3/4" union |
| Hot water [number]   | 1 x 3/4" with 1" union      |
| Hard water (optional) [number]   | 2 x 1/2" w/ 3/4" union      |
| Drain valve  | DN 70                       |
| <b>Dimensions and weight</b>   |                             |
| External dimensions, net height in in. (mm)  | 53 3/16 (1350)              |
| External dimensions, net width in in. (mm)   | 31 1/2 (799)                |
| External dimensions, net depth in in. (mm)   | 40 3/8 (1024)               |
| External dimensions, gross height in in. (mm)  | 58 5/16 (1480)              |
| External dimensions, gross width in in. (mm)   | 47 11/16 (1210)             |
| External dimensions, gross depth in in. (mm)   | 44 1/2 (1130)               |
| Net weight in lbs. (kg)  | 627 (284.0)                 |
| Gross weight in lbs. (kg)  | 677 (307)                   |
| Maximum floor load in N/m <sup>2</sup>   | 4483                        |
| <b>Emission values</b>   |                             |
| Emission sound pressure level in the workplace   | 65 dB(A) re 20 µPa          |
| Heat dissipation into the room in MJ/h   | 6.48                        |
| <b>Features</b>  |                             |
| Patented pre-spin  | •                           |
| Cloths treatment   | •                           |
| 3-dimensional imbalance monitoring   | •                           |

PWM 912 [EH DV DD]

Professional washing machine, external heating  
with detergent drawer, M Touch Pro Plus – freely programmable.



EAN: 4002516444701 / Material number: 11803080 / Old Material Number: 51912059NAM

|  |     |
|--|-----|
| Efficient scoop ribs                                 | •   |
| EcoSpeed   | •   |
| Spring-in-spring system                              | •   |
| Temperature monitoring                               | •   |
| Automatic load recognition+                          | •   |
| Volumetric flow meter (optional)                     | •   |
| Weighing base (optional)                             | •   |
| Adding laundry                                       | •   |
| Program selection via colour frame                   | •   |
| Emergency shut-off                                   | •   |
| Machine-independent accessories                      | •   |
| <b>Efficiency and sustainability</b>                 |     |
| Recycling rate in %                                  | 91  |
| <b>Connection options</b>                            |     |
| Payment system (optional)                            | •   |
| Optical interface for service access                 | •   |
| Peak-load negotiation / energy management (optional) | •   |
| Water recovery (optional)                            | •   |
| LAN  | •   |
| Wi-Fi  | •   |
| Connector Box  | •   |
| <b>Capacities</b>                                    |     |
| Breathing masks [number]                             | 10  |
| Helmets [number]                                     | 3   |
| Protective suits [number]                            | 2   |
| Protective coats [number]                            | 3   |
| Chemical protection suits [number]                   | 1   |
| Synthetic duvets [number]                            | 1   |
| Synthetic pillows [number]                           | 2   |
| Down comforters [number]                             | 1   |
| Down pillows [number]                                | 2   |
| Cleaning cloths, 22 g [number]                       | 289 |
| Cotton mops, 40 cm / 190 g [number]                  | 100 |
| Cotton mops, 50 cm / 220 g [number]                  | 72  |
| Microfibre mops, 40 cm / 120 g [number]              | 102 |
| Microfibre mops, 50 cm / 170 g [number]              | 72  |
| Mops, office, 100 g [number]                         | 120 |
| Mops, stairway, 150 g [number]                       | 80  |
| Horse summer blankets [number]                       | 2   |
| <b>Standards / certs / symbols</b>                   |     |
| Splash protection IPX4                               | •   |
| c ETL US   | •   |
| Complies with Machinery Directive 2006/42/EC         | •   |