

## PWM 916 [SI DV DD]

Professional washing machine, steam heating (indirect)  
with detergent drawer, M Touch Pro Plus – freely programmable.



- Drum volume 4.94 (140) ft<sup>3</sup> (l), load size 35 (15.5) lb (kg)
- Top cleaning & consumption values – innovative Miele technology
- Ideal operation thanks to touch colour display – M Touch Pro Plus
- Simple and safe operation thanks to automatic door lock
- Connected for the future using LAN and Wi-Fi

EAN: 4002516445135 / Material number: 11803260 / Old Material Number: 51916049NAM

### Construction type and design

Construction type	Front loader
Product line	Performance Plus
Front	Stainless steel
Control panel colour	Stainless steel
Maximum load with a load ratio of 1:9 in lbs (kg)	36 (16.0)
Load ratio	1:9
Load in lbs. (kg)	35 (15.5)
Drum volume in l	4.94 (140) ft <sup>3</sup> (l)
Door opening [Ø] in in. (mm)	16 3/8 (415)
Door-opening angle in degrees	180
Door hinging	right
Automatic door lock	•
Innovative suds container	•
Maintenance-free motor with frequency converter	•
Patented honeycomb drum 2.0	•

### Application

Suitable for hotels and restaurants	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundromats	•
Suitable for small businesses	•
Suitable for fire departments and rescue services	•
Suitable for stud farms and stables	•
Suitable for universities, schools, and kindergartens	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for the petrochemical industry	•
Suitable for amusement parks and holiday resorts	•
Suitable for public / community facilities	•

### Performance data

Tested virucidal efficacy	•
Proven hygiene	•
Specific water consumption for cold water connection in l/kg	6.20
Specific energy consumption for cold water connection in kWh/kg	0.14
Specific water consumption for hot water connection in l/kg	5.90
Specific energy consumption for hot water connection in kWh/kg	0.06
Water consumption with cold water connection in l	99.2
Water consumption for cold water connection in Mops standard 60°C program in l	182.2
Energy consumption with cold water connection in kWh	2.26
Energy consumption for cold water connection in Mops standard 60°C program in kWh	3.21
Program duration with cold water connection in minutes	46
Water consumption with hot water connection in l	94.4

PWM 916 [SI DV DD]

Professional washing machine, steam heating (indirect)  
with detergent drawer, M Touch Pro Plus – freely programmable.



EAN: 4002516445135 / Material number: 11803260 / Old Material Number: 51916049NAM

Water consumption for hot water connection in Mops standard 60°C program in l	178.1
Energy consumption with hot water connection in kWh	0.96
Energy consumption for hot water connection in Mops standard 60°C program in kWh	1.33
Program duration with hot water connection in minutes	42
Water consumption in Economy program with cold water connection in l	92.8
Energy consumption in Economy program with cold water connection in kWh	1.48
Program duration with cold water connection in Economy program in minutes	33
Water consumption in Economy program with hot water connection in l	91.2
Energy consumption in Economy program with hot water connection in kWh	0.48
Program duration with hot water connection in Economy program in minutes	32
Program cycle time in minutes for Mops standard 60°C program with cold water connection	50
Program cycle time in minutes for Mops standard 60°C program with hot water connection	47
Residual moisture with cold rinse in %	48
Residual moisture with hot rinse in %	44
Residual moisture when reprocessing wiping cloths in %	25
Spin speed in rpm	1075
g-factor	462
Tested operating hours	30000
<b>Controls</b>	
Control type	M Touch Pro Plus
Programmability	Freely programmable
Max. delay start in h	Can be selected freely
Time left display	•
Program sequence indicator	•
Choice of display language	•
Option to enter weight prior to start of program	•
<b>Standard / target grp programs</b>	
Basic programs	•
<b>Dispensing</b>	
Detergent drawer	3 compartments
Maximum number of connections for liquid dispenser pumps [number]	12
Empty sensing	•
<b>Standard electrical connection</b>	
Heating type	Indirect steam
Electrical connection	240V 60HZ 1 PH 3 WIRE
Steam heater rating in kW	37.00
Total rated load in kW	2.30
Fuse rating in A	20
<b>Water connection/drainage</b>	
Cold water [number]	3 x 1/2" hose w/ 3/4" union

PWM 916 [SI DV DD]

Professional washing machine, steam heating (indirect)  
with detergent drawer, M Touch Pro Plus – freely programmable.

EAN: 4002516445135 / Material number: 11803260 / Old Material Number: 51916049NAM

Hot water [number]	1x 1/2" hose w/ 3/4" th. union
Hard water (optional) [number]	2 x 1/2" w/ 3/4" union
Drain valve	DN 70
<b>Steam connection</b>	
Steam connection	2 x 1/2"
<b>Dimensions and weight</b>	
External dimensions, net height in in. (mm)	57 1/8 (1450)
External dimensions, net width in in. (mm)	36 7/16 (924)
External dimensions, net depth in in. (mm)	37 9/16 (954)
External dimensions, gross height in in. (mm)	62 7/16 (1585)
External dimensions, gross width in in. (mm)	47 11/16 (1210)
External dimensions, gross depth in in. (mm)	44 1/2 (1130)
Net weight in lbs. (kg)	779 (353.0)
Gross weight in lbs. (kg)	829 (376)
Maximum floor load in N/m <sup>2</sup>	5209
<b>Emission values</b>	
Emission sound pressure level in the workplace	65 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	6.48
<b>Features</b>	
Patented pre-spin	•
Cloths treatment	•
3-dimensional imbalance monitoring	•
Disinfection rinse	•
Efficient scoop ribs	•
EcoSpeed	•
Spring-in-spring system	•
Temperature monitoring	•
Automatic load recognition+	•
Volumetric flow meter (optional)	•
Adding laundry	•
Program selection via colour frame	•
Emergency shut-off	•
Machine-independent accessories	•
<b>Efficiency and sustainability</b>	
Recycling rate in %	92
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
Water recovery (optional)	•
LAN	•
Wi-Fi	•
Connector Box	•
<b>Capacities</b>	
Breathing masks [number]	13
Helmets [number]	4
Protective suits [number]	2
Protective coats [number]	3
Chemical protection suits [number]	1
Synthetic duvets [number]	1

PWM 916 [SI DV DD]

Professional washing machine, steam heating (indirect)  
with detergent drawer, M Touch Pro Plus – freely programmable.



EAN: 4002516445135 / Material number: 11803260 / Old Material Number: 51916049NAM

Synthetic pillows [number]	3
Down comforters [number]	1
Down pillows [number]	3
Cleaning cloths, 22 g [number]	355
Cotton mops, 40 cm / 190 g [number]	82
Cotton mops, 50 cm / 220 g [number]	71
Microfibre mops, 40 cm / 120 g [number]	130
Microfibre mops, 50 cm / 170 g [number]	91
Mops, office, 100 g [number]	160
Mops, stairway, 150 g [number]	105
Horse summer blankets [number]	3
<b>Standards / certs / symbols</b>	
Splash protection IPX4	•
c ETL US	•
Complies with Machinery Directive 2006/42/EC	•