

## APLW DS7111

### Installation kit

liquid dispensing for retrofitting of the PLW 7111 with a third dispenser pump.

EAN: 4002516648697 / Material number: 11993930 / Old Material Number: 69242001D



- Can be retrofitted by Customer Service
- For the use of additional process chemicals
- A maximum of two retrofitting kits can be fitted

| Product category                                   |                               |
|----------------------------------------------------|-------------------------------|
| SlimLine laboratory glassware washers              | •                             |
| Machine affiliation                                |                               |
| PLW 7111                                           | •                             |
| PLW 7111 [Safety]                                  | •                             |
| PWD 7121                                           | •                             |
| PWD 7122                                           | •                             |
| Product category                                   |                               |
| Conversion kit                                     | •                             |
| Dispenser system                                   | •                             |
| Product characteristics                            |                               |
| Material                                           | Stainless steel, Plastic      |
| Colour                                             | Stainless Steel, Green, Black |
| Application area                                   |                               |
| Reprocessing of laboratory glassware               | •                             |
| Reprocessing of dental instruments                 | •                             |
| Reprocessing of lumened instruments                | •                             |
| Reprocessing of trays                              | •                             |
| Reprocessing of air regulators                     | •                             |
| Reprocessing of breathing masks                    | •                             |
| Reprocessing of compressed air unit carrier frames | •                             |
| Reprocessing of compressed air bottles             | •                             |
| Dimensions and weight                              |                               |
| External dimensions, gross height in in. (mm)      | 3 3/4 (95)                    |
| External dimensions, gross width in in. (mm)       | 6 3/4 (170)                   |
| External dimensions, gross depth in in. (mm)       | 21 11/16 (550)                |
| Net weight in lb (kg)                              | 1 (0.42)                      |
| Gross weight in lb (kg)                            | 2 (0.64)                      |