

## PDR 914 [G]

Professional vented dryer, gas heating  
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 8.83 (250.00) ft<sup>3</sup> (l), load size 23 (10.0) lb (kg) – 31 (14.0) lb (kg)
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and Wi-Fi

EAN: 4002516544593 / Material number: 12012120 / Old Material Number: 52914019NAM

Construction type and design	
Construction type	Front loader
Product line	Performance Plus
Front	Stainless steel
Load size with a load ratio of 1:25	23 (10.0)
Load size with a load ratio of 1:18	30 (13.5)
Drum volume in l	8.83 (250.00) ft <sup>3</sup> (l)
Drying system	Vented system
Door opening [Ø] in in. (mm)	20 1/2 (520)
Door-opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes
Application	
Suitable for hotels and restaurants	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundromats	•
Suitable for fire departments and rescue services	•
Suitable for stud farms and stables	•
Suitable for universities, schools, and kindergartens	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for medical and dental practices	•
Suitable for the petrochemical industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks and holiday resorts	•
Suitable for public / community facilities	•
Performance data	
Maximum evaporation capacity in l/hour	14 (14) gal (US)/min (l)
Specific energy consumption in kWh/kg	0.55
Program duration in minutes	23
Tested operating hours	20000
Controls	
Control type	M Touch Pro
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Program sequence indicator	•
Choice of display language	•
Standard electrical connection	
Heating type	Gas
Electrical connection	208/240 V 60 HZ 2 PH
Electric heater rating in kW	0.00
Gas heater rating in kW	15.00
Total rated load in kW	0.60

PDR 914 [G]

Professional vented dryer, gas heating

with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516544593 / Material number: 12012120 / Old Material Number: 52914019NAM

Fuse rating in A	15
<b>Dimensions and weight of dryer</b>	
External dimensions, net height in in. (mm)	55 1/8 (1400)
External dimensions, net width in in. (mm)	35 11/16 (906)
External dimensions, net depth in in. (mm)	33 9/16 (852)
External dimensions, gross height in in. (mm)	60 1/8 (1526)
External dimensions, gross width in in. (mm)	42 15/16 (1090)
External dimensions, gross depth in in. (mm)	36 15/16 (938)
Net weight in lbs. (kg)	359 (162.4)
Gross weight in lbs. (kg)	384 (174)
Maximum floor load in N/m <sup>2</sup>	2044
<b>Emission values</b>	
Emission sound pressure level in the workplace	51 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.90
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface lint filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling	•
Communication slot	•
Program selection via colour frame	•
Emergency shut-off	•
Machine-independent accessories	•
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
Wi-Fi dryer	•
Connector Box	•
LAN module (optional)	•
<b>Capacities</b>	
Breathing masks [number]	8
Protective suits [number]	1
Protective coats [number]	2
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Down comforters [number]	1
Down pillows [number]	2
Cleaning cloths, 22 g [number]	255
Cotton mops, 40 cm [number]	53
Cotton mops, 50 cm [number]	45
Microfibre mops, 40 cm [number]	83
Microfibre mops, 50 cm [number]	59
Horse summer blankets [number]	2
<b>Standards / certs / symbols</b>	
Splash protection IPX4	•
c ETL US	•
Complies with Machinery Directive 2006/42/EC	•