

## PDR 918 [SI]

Professional vented dryer, steam heating  
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 11.48 (325.00) ft<sup>3</sup> (l), load size 29 (13.0) lb (kg) kg – 40 (18.0) lb (kg) kg
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling Plus
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and Wi-Fi

EAN: 4002516546436 / Material number: 12012210 / Old Material Number: 52918026NAM

| <b>Construction type and design</b>                   |                                    |
|---|------------------------------------|
| Construction type                                     | Front loader                       |
| Product line  | Performance Plus                   |
| Front   | Iron grey                          |
| Load size with a load ratio of 1:25                   | 29 (13.0) lb (kg)                  |
| Load size with a load ratio of 1:18                   | 40 (18.0) lb (kg)                  |
| Drum volume in l                                      | 11.48 (325.00) ft <sup>3</sup> (l) |
| Drying system   | Vented system                      |
| Door opening [Ø] in in. (mm)                          | 20 1/2 (520)                       |
| Door-opening angle in degrees                         | 180                                |
| Door hinging  | left                               |
| Convertible hinging                                   | •                                  |
| Stainless steel honeycomb drum                        | Yes                                |
| <b>Application</b>                                    |                                    |
| Suitable for hotels and restaurants                   | •                                  |
| Suitable for retirement and care homes                | •                                  |
| Suitable for facility management                      | •                                  |
| Suitable for dry cleaners                             | •                                  |
| Suitable for commercial laundromats                   | •                                  |
| Suitable for fire departments and rescue services     | •                                  |
| Suitable for stud farms and stables                   | •                                  |
| Suitable for universities, schools, and kindergartens | •                                  |
| Suitable for hospitals                                | •                                  |
| Suitable for sports clubs                             | •                                  |
| Suitable for beauty salons, spas, and fitness centres | •                                  |
| Suitable for medical and dental practices             | •                                  |
| Suitable for the petrochemical industry               | •                                  |
| Suitable for the food-processing industry             | •                                  |
| Suitable for amusement parks and holiday resorts      | •                                  |
| Suitable for public / community facilities            | •                                  |
| <b>Performance data</b>                               |                                    |
| Maximum evaporation capacity in l/hour                | 15 (15) gal (US)/min (l)           |
| Specific energy consumption in kWh/kg                 | 0.64                               |
| Program duration in minutes                           | 29                                 |
| Tested operating hours                                | 20000                              |
| <b>Controls</b>                                       |                                    |
| Control type  | M Touch Pro                        |
| Programmability                                       | programmable                       |
| Program controls                                      | Residual moisture controlled       |
| Max. delay start in h                                 | 24                                 |
| Time left display                                     | •                                  |
| Program sequence indicator                            | •                                  |
| Choice of display language                            | •                                  |
| <b>Standard electrical connection</b>                 |                                    |
| Heating type  | Indirect steam                     |
| Electrical connection                                 | 208/240 V 60 HZ 2 PH               |
| Electric heater rating in kW                          | 0.00                               |
| Steam heater rating in kW                             | 28.00                              |
| Total rated load in kW                                | 0.60                               |

## PDR 918 [SI]

Professional vented dryer, steam heating

with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516546436 / Material number: 12012210 / Old Material Number: 52918026NAM

|  |                    |
|--|--------------------|
| Fuse rating in A                                     | 15                 |
| <b>Dimensions and weight</b>                         |                    |
| External dimensions, net height in in. (mm)          | 55 1/8 (1400)      |
| External dimensions, net width in in. (mm)           | 35 11/16 (906)     |
| External dimensions, net depth in in. (mm)           | 40 3/4 (1035)      |
| External dimensions, gross height in in. (mm)        | 60 1/8 (1526)      |
| External dimensions, gross width in in. (mm)         | 42 15/16 (1090)    |
| External dimensions, gross depth in in. (mm)         | 44 5/16 (1125)     |
| Net weight in lbs. (kg)                              | 458 (207.5)        |
| Gross weight in lbs. (kg)                            | 488 (221)          |
| Maximum floor load in N/m <sup>2</sup>               | 2546               |
| <b>Emission values</b>                               |                    |
| Emission sound pressure level in the workplace       | 50 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h               | 4.50               |
| <b>Features</b>                                      |                    |
| Intelligent drum reversal                            | •                  |
| Axial airflow  | •                  |
| Large-surface lint filter                            | •                  |
| PerfectDry   | •                  |
| SoftLift drum ribs                                   | •                  |
| AirRecycling   | •                  |
| Communication slot                                   | •                  |
| Program selection via colour frame                   | •                  |
| Emergency shut-off                                   | •                  |
| Machine-independent accessories                      | •                  |
| <b>Connection options</b>                            |                    |
| Payment system (optional)                            | •                  |
| Optical interface for service access                 | •                  |
| Peak-load negotiation / energy management (optional) | •                  |
| Wi-Fi dryer  | •                  |
| Connector Box  | •                  |
| LAN module (optional)                                | •                  |
| <b>Capacities</b>                                    |                    |
| Breathing masks [number]                             | 12                 |
| Protective suits [number]                            | 2                  |
| Protective coats [number]                            | 3                  |
| Synthetic duvets [number]                            | 1                  |
| Synthetic pillows [number]                           | 3                  |
| Down comforters [number]                             | 1                  |
| Down pillows [number]                                | 3                  |
| Cleaning cloths, 22 g [number]                       | 295                |
| Cotton mops, 40 cm [number]                          | 68                 |
| Cotton mops, 50 cm [number]                          | 59                 |
| Microfibre mops, 40 cm [number]                      | 108                |
| Microfibre mops, 50 cm [number]                      | 76                 |
| Horse summer blankets [number]                       | 3                  |
| <b>Standards / certs / symbols</b>                   |                    |
| Splash protection IPX4                               | •                  |
| c ETL US   | •                  |
| Complies with Machinery Directive 2006/42/EC         | •                  |