

PDR 918 [G]

Professional vented dryer, gas heating
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 11.48 (325.00) ft³ (l)
l, load size 29 (13.0) lb (kg) kg – 40
(18.0) lb (kg) kg
- Unique, gentle fabric care –
honeycomb drum
- Greatest energy efficiency thanks to
Air Recycling
- Precision drying of all fabrics –
PerfectDry
- Connected for the future using LAN
and Wi-Fi

EAN: 4002516546450 / Material number: 12012240 / Old Material Number: 52918028NAM

| Construction type and design | |
|---|------------------------------------|
| Construction type | Front loader |
| Product line | Performance Plus |
| Front | Iron grey |
| Load size with a load ratio of 1:25 | 29 (13.0) lb (kg) |
| Load size with a load ratio of 1:18 | 40 (18.0) lb (kg) |
| Drum volume in l | 11.48 (325.00) ft ³ (l) |
| Drying system | Vented system |
| Door opening [Ø] in in. (mm) | 20 1/2 (520) |
| Door-opening angle in degrees | 180 |
| Door hinging | left |
| Convertible hinging | • |
| Stainless steel honeycomb drum | Yes |
| Application | |
| Suitable for hotels and restaurants | • |
| Suitable for retirement and care homes | • |
| Suitable for facility management | • |
| Suitable for dry cleaners | • |
| Suitable for commercial laundromats | • |
| Suitable for fire departments and rescue services | • |
| Suitable for stud farms and stables | • |
| Suitable for universities, schools, and kindergartens | • |
| Suitable for hospitals | • |
| Suitable for sports clubs | • |
| Suitable for beauty salons, spas, and fitness centres | • |
| Suitable for medical and dental practices | • |
| Suitable for the petrochemical industry | • |
| Suitable for the food-processing industry | • |
| Suitable for amusement parks and holiday resorts | • |
| Suitable for public / community facilities | • |
| Performance data | |
| Maximum evaporation capacity in l/hour | 17 (17) gal (US)/min (l) |
| Specific energy consumption in kWh/kg | 0.56 |
| Program duration in minutes | 26 |
| Tested operating hours | 20000 |
| Controls | |
| Control type | M Touch Pro |
| Programmability | programmable |
| Program controls | Residual moisture controlled |
| Max. delay start in h | 24 |
| Time left display | • |
| Program sequence indicator | • |
| Choice of display language | • |
| Standard electrical connection | |
| Heating type | Gas |
| Electrical connection | 208/240 V 60 HZ 2 PH |
| Electric heater rating in kW | 0.00 |
| Gas heater rating in kW | 18.00 |
| Total rated load in kW | 0.60 |

PDR 918 [G]

Professional vented dryer, gas heating

with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516546450 / Material number: 12012240 / Old Material Number: 52918028NAM

| | |
|--|--------------------|
| Fuse rating in A | 15 |
| Dimensions and weight | |
| External dimensions, net height in in. (mm) | 55 1/8 (1400) |
| External dimensions, net width in in. (mm) | 35 11/16 (906) |
| External dimensions, net depth in in. (mm) | 40 3/4 (1035) |
| External dimensions, gross height in in. (mm) | 60 1/8 (1526) |
| External dimensions, gross width in in. (mm) | 42 15/16 (1090) |
| External dimensions, gross depth in in. (mm) | 44 5/16 (1125) |
| Net weight in lbs. (kg) | 396 (179.5) |
| Gross weight in lbs. (kg) | 426 (193) |
| Maximum floor load in N/m ² | 2271 |
| Emission values | |
| Emission sound pressure level in the workplace | 50 dB(A) re 20 µPa |
| Heat dissipation into the room in MJ/h | 4.50 |
| Features | |
| Intelligent drum reversal | • |
| Axial airflow | • |
| Large-surface lint filter | • |
| PerfectDry | • |
| SoftLift drum ribs | • |
| AirRecycling | • |
| Communication slot | • |
| Program selection via colour frame | • |
| Emergency shut-off | • |
| Machine-independent accessories | • |
| Connection options | |
| Payment system (optional) | • |
| Optical interface for service access | • |
| Peak-load negotiation / energy management (optional) | • |
| Wi-Fi dryer | • |
| Connector Box | • |
| LAN module (optional) | • |
| Capacities | |
| Breathing masks [number] | 12 |
| Protective suits [number] | 2 |
| Protective coats [number] | 3 |
| Synthetic duvets [number] | 1 |
| Synthetic pillows [number] | 3 |
| Down comforters [number] | 1 |
| Down pillows [number] | 3 |
| Cleaning cloths, 22 g [number] | 295 |
| Cotton mops, 40 cm [number] | 68 |
| Cotton mops, 50 cm [number] | 59 |
| Microfibre mops, 40 cm [number] | 108 |
| Microfibre mops, 50 cm [number] | 76 |
| Horse summer blankets [number] | 3 |
| Standards / certs / symbols | |
| Splash protection IPX4 | • |
| c ETL US | • |
| Complies with Machinery Directive 2006/42/EC | • |