

## PDR 928 [EL]

Professional vented dryer, electric heating

with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 17.66 (500.00) ft<sup>3</sup> (l), load size 45 (20.0) lb (kg) – 62 (28.0) lb (kg)
- Unique, gentle fabric care – honeycomb drum
- Greatest energy efficiency thanks to Air Recycling
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and Wi-Fi

EAN: 4002516546610 / Material number: 12012390 / Old Material Number: 52928024NAM

### Construction type and design

Construction type	Front loader
Product line	Performance Plus
Front	Stainless steel
Load size with a load ratio of 1:25	45 (20.0)
Load size with a load ratio of 1:18	60 (27.0)
Drum volume in l	17.66 (500.00) ft <sup>3</sup> (l)
Drying system	Vented system
Door opening [Ø] in in. (mm)	20 1/2 (520)
Door-opening angle in degrees	180
Door hinging	left
Convertible hinging	•
Stainless steel honeycomb drum	Yes

### Application

Suitable for hotels and restaurants	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundromats	•
Suitable for fire departments and rescue services	•
Suitable for stud farms and stables	•
Suitable for universities, schools, and kindergartens	•
Suitable for hospitals	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for medical and dental practices	•
Suitable for the petrochemical industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks and holiday resorts	•
Suitable for public / community facilities	•

### Performance data

Maximum evaporation capacity in l/hour	27 (27) gal (US)/min (l)
Specific energy consumption in kWh/kg	0.59
Program duration in minutes	24
Tested operating hours	20000

### Controls

Control type	M Touch Pro
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Program sequence indicator	•
Choice of display language	•

### Standard electrical connection

Heating type	Electric
Electrical connection	440/480 V 60 HZ 3 PH
Electric heater rating in kW	31.80
Total rated load in kW	33.00
Fuse rating in A	60

PDR 928 [EL]

Professional vented dryer, electric heating

with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516546610 / Material number: 12012390 / Old Material Number: 52928024NAM

Dimensions and weight of dryer	
External dimensions, net height in in. (mm)	64 5/8 (1640)
External dimensions, net width in in. (mm)	47 1/2 (1206)
External dimensions, net depth in in. (mm)	40 1/8 (1019)
External dimensions, gross height in in. (mm)	69 9/16 (1766)
External dimensions, gross width in in. (mm)	54 3/4 (1390)
External dimensions, gross depth in in. (mm)	43 5/8 (1108)
Net weight in lbs. (kg)	537 (243.3)
Gross weight in lbs. (kg)	569 (258)
Maximum floor load in N/m <sup>2</sup>	3044
Emission values	
Emission sound pressure level in the workplace	58 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.30
Features	
Intelligent drum reversal	•
Axial airflow	•
Large-surface lint filter	•
PerfectDry	•
SoftLift drum ribs	•
AirRecycling	•
Communication slot	•
Program selection via colour frame	•
Emergency shut-off	•
Machine-independent accessories	•
Connection options	
Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
Wi-Fi dryer	•
Connector Box	•
LAN module (optional)	•
Capacities	
Breathing masks [number]	12
Protective suits [number]	3
Protective coats [number]	5
Synthetic duvets [number]	2
Synthetic pillows [number]	3
Down comforters [number]	2
Down pillows [number]	5
Cleaning cloths, 22 g [number]	545
Cotton mops, 40 cm [number]	105
Cotton mops, 50 cm [number]	91
Microfibre mops, 40 cm [number]	167
Microfibre mops, 50 cm [number]	118
Horse summer blankets [number]	3
Standards / certs / symbols	
Splash protection IPX4	•
c ETL US	•
Complies with Machinery Directive 2006/42/EC	•