

PFD 404 U [240V]

Built-under fresh-water dishwasher

with baskets, for care homes, nursery schools & all with high hygiene needs.



- Max. cleaning performance*: 380 plates/h or 20 baskets/h
- First-class results thanks to freshwater wash system
- Extremely hygienic results – final rinse temperature of 185 (85) °F (°C)
- Safe and easy operation – automatic door opening
- Max. user convenience with M Touch Flex full-touch colour display

* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

EAN: 4002516577379 / Material number: 12066600 / Old Material Number: 61040435NAM

Construction type and design	
Construction type	Built-under dishwasher
Product line	MasterLine
Model	Hygiene
Wash system	Fresh water dishwasher
Number of wash levels	2
Front	Stainless steel
Lid	Without lid
Side panels	Galvanised
Application	
Suitable for retirement and care homes	•
Suitable for hospitals	•
Suitable for kindergartens	•
Suitable for universities and schools	•
Performance data	
Tested virucidal efficacy	•
Proven hygiene	•
Circulation pump, Qmax in gal/min (l/min.)	103 (390)
Shortest program duration in minutes	6
Maximum final rinse temperature in °F (°C)	185 (85)
Cleaning performance, plates/h	380
Cleaning performance, baskets/h	20
Possible to wash plastic baskets on 2 levels	•
Service life in wash cycles	28000
Controls	
Control type	M Touch Flex
Max. delay start in h	24
Time left display	•
Programs [quantity]	12
Program sequence indicator	•
Choice of display language	•
Language-neutral operation	•
Standard electrical connection	
Electrical connection	2 AC 240V 60HZ
Heater rating in kW	5.40
Total rated load in kW	5.80
Fuse rating in A	30
Length of power cord in ft. (m)	6 (1.90)
NEMA plug: Twist Lock L6-30	•
Possible voltage variant 1	
Electrical connection	3 AC 240V 60HZ
Heater rating in kW	5.40
Total rated load in kW	5.80
Fuse rating in A	20
Water connection/drainage	
Cold water [number]	1
Hot water [number]	1
Required flow pressure in bar	1.00-10.00
Drain pump [DN]	22
Maximum drain pump height (delivery head) in in. (cm)	39 3/8 (100)

PFD 404 U [240V]

Built-under fresh-water dishwasher

with baskets, for care homes, nursery schools & all with high hygiene needs.



EAN: 4002516577379 / Material number: 12066600 / Old Material Number: 61040435NAM

Integrated water softener	•
Maximum water hardness in (mmol/l)	62.59 (10.70)
Water protection system	Waterproof system
Water consumption per wash cycle in l	2.1 (8.00) gll (l)
Length of water inlet hose in in. (cm)	67 (170)
Length of water drain hose in in. (cm)	59 1/8 (150)
Dimensions and weight	
External dimensions, height in in. (mm)	32 5/16 (820)
External dimensions, width in in. (mm)	23 9/16 (598)
External dimensions, depth in in. (mm)	23 7/16 (595)
External dimensions, gross height in in. (mm)	36 1/4 (920)
External dimensions, gross width in in. (mm)	26 7/16 (670)
External dimensions, gross depth in in. (mm)	29 3/16 (740)
Usable space in wash cabinet, height in in. (mm)	22 1/16 (559)
Usable space in wash cabinet, width in in. (mm)	21 1/8 (536)
Usable space in wash cabinet, depth of upper basket in in. (mm)	18 11/16 (474)
Usable space in wash cabinet, depth of lower basket in in. (mm)	20 3/8 (516)
Rack height above floor in in. (mm)	8 9/16 (216)
Required niche width in in. (mm)	23 5/8 (600)
Net weight lb [kg]	166 (75)
Gross weight in lb (kg)	188 (85)
Maximum floor load in N/m ²	1200
Emission values	
Emission sound pressure level at workplace (LpA)	45 dB(A) re 20 µPa
Sound power level LwA	57.0
Heat dissipation into the room in MJ/h	1.44
Programs	
Universal	•
Super short	•
Short	•
SaniWash	•
Hygiene Plus	•
Cold / pre-wash	•
Glasses	•
Beer glasses	•
Cutlery	•
Plastics	•
Intensive	•
Reactivation	•
Drainage by pump	•
Basket design	
2 x insert E 816 for plates	•
1 x APFD 215 upper basket	•
1 x APFD 220 lower basket for inserts	•
2 x APFD 420 insert for cutlery	•
Height-adjustable upper basket	•
Combinable with APFD 210 bottle basket	•
Features	
Drying	AutoOpen assisted drying

PFD 404 U [240V]

Built-under fresh-water dishwasher

with baskets, for care homes, nursery schools & all with high hygiene needs.



EAN: 4002516577379 / Material number: 12066600 / Old Material Number: 61040435NAM

1 combi dispensing unit in the door for powder cleaning agent and rinsing agent •

Wash cabinet made of high-quality stainless steel •

In-door salt container •

AutoClose •

Perfect GlassCare •

Aerosol steam condenser •

Door lock, protected by code •

Adjustable temperature holding time •

Adjustable final rinse temperature •

Optical interface •

Highly effective filter system with filter monitoring •

A wide range of accessories (optional) •

Connection options

External dispenser module for liquid cleaning agent •

Standards / certs / symbols

Complies with Machinery Directive 2006/42/EC •

Splash protection IPX1 •

EMC radio suppressed •

DIN 10512 •

DIN EN 17735 •

ETL •

ADA •