

## PFD 408 U [240V]

Built-under fresh-water dishwasher

With baskets, for high hygiene requirements (NSF/ANSI 3). ADA compliant.



- Max. cleaning performance\*: 152 plates/h
- First-class results thanks to freshwater wash system
- Extremely hygienic results – final rinse temperature of 185 (85) °F (°C)
- Safe and easy operation – automatic door opening
- Versatile processing of two wire or plastic baskets per cycle

\* Depending on site conditions (temperature of incoming water / power connection) values given may vary.

EAN: 4002516577386 / Material number: 12066610 / Old Material Number: 61040835NAM

Construction type and design	
Construction type	Built-under dishwasher
Product line	MasterLine
Model	HygienePro
Wash system	Fresh water dishwasher
Number of wash levels	2
Front	Stainless steel
Lid	Without lid
Side panels	Galvanised
Application	
Suitable for retirement and care homes	•
Suitable for small restaurants/bars	•
Suitable for the hospitality industry	•
Suitable for guesthouses	•
Suitable for cafeterias	•
Suitable for kindergartens	•
Suitable for fast food restaurants	•
Performance data	
Circulation pump, Qmax in gal/min (l/min.)	103 (390)
Shortest program duration in minutes	15
Maximum final rinse temperature in °F (°C)	185 (85)
Cleaning performance, plates/h	152
Cleaning performance, baskets/h	8
Possible to wash plastic baskets on 2 levels	•
Service life in wash cycles	28000
Controls	
Control type	M Touch Flex
Max. delay start in h	24
Time left display	•
Programs [quantity]	4
Program sequence indicator	•
Choice of display language	•
Language-neutral operation	•
Standard electrical connection	
Electrical connection	3 AC 240V 60HZ
Heater rating in kW	5.40
Total rated load in kW	5.80
Fuse rating in A	20
Length of power cord in ft. (m)	6 (1.90)
NEMA plug: Twist Lock L15-20	•
Possible voltage variant 1	
Electrical connection	2 AC 240V 60HZ
Heater rating in kW	5.40
Total rated load in kW	5.80
Fuse rating in A	30
Water connection/drainage	
Cold water [number]	1
Hot water [number]	1
Required flow pressure in bar	0.40-10.00
Drain pump [DN]	22

## PFD 408 U [240V]

Built-under fresh-water dishwasher

With baskets, for high hygiene requirements (NSF/ANSI 3). ADA compliant.



EAN: 4002516577386 / Material number: 12066610 / Old Material Number: 61040835NAM

Maximum drain pump height (delivery head) in in. (cm)	39 3/8 (100)
Integrated water softener	•
Maximum water hardness in (mmol/l)	62.59 (10.70)
Water protection system	Waterproof system
Water consumption per wash cycle in l	4.6 (17.50) gll (l)
Length of water inlet hose in in. (cm)	67 (170)
Length of water drain hose in in. (cm)	59 1/8 (150)
<b>Dimensions and weight</b>	
External dimensions, height in in. (mm)	32 5/16 (820)
External dimensions, width in in. (mm)	23 9/16 (598)
External dimensions, depth in in. (mm)	23 7/16 (595)
External dimensions, gross height in in. (mm)	36 1/4 (920)
External dimensions, gross width in in. (mm)	26 7/16 (670)
External dimensions, gross depth in in. (mm)	29 3/16 (740)
Usable space in wash cabinet, height in in. (mm)	22 1/16 (559)
Usable space in wash cabinet, width in in. (mm)	21 1/8 (536)
Usable space in wash cabinet, depth of upper basket in in. (mm)	18 11/16 (474)
Usable space in wash cabinet, depth of lower basket in in. (mm)	20 3/8 (516)
Rack height above floor in in. (mm)	8 9/16 (216)
Required niche width in in. (mm)	23 5/8 (600)
Net weight lb [kg]	166 (75)
Gross weight in lb (kg)	188 (85)
Maximum floor load in N/m <sup>2</sup>	1200
<b>Emission values</b>	
Emission sound pressure level at workplace (LpA)	45 dB(A) re 20 µPa
Sound power level LwA	57.0
Heat dissipation into the room in MJ/h	1.44
<b>Programs</b>	
Universal	•
Short	•
Cold / pre-wash	•
Intensive	•
Reactivation	•
Drainage by pump	•
<b>Basket design</b>	
2 x insert E 816 for plates	•
1 x APFD 215 upper basket	•
1 x APFD 220 lower basket for inserts	•
2 x APFD 420 insert for cutlery	•
Height-adjustable upper basket	•
Combinable with APFD 210 bottle basket	•
<b>Features</b>	
Drying	AutoOpen assisted drying
1 combi dispensing unit in the door for powder cleaning agent and rinsing agent	•
Wash cabinet made of high-quality stainless steel	•
In-door salt container	•
AutoClose	•
Aerosol steam condenser	•

PFD 408 U [240V]

Built-under fresh-water dishwasher

With baskets, for high hygiene requirements (NSF/ANSI 3). ADA compliant.



EAN: 4002516577386 / Material number: 12066610 / Old Material Number: 61040835NAM

Door lock, protected by code	•
Adjustable temperature holding time	•
Adjustable final rinse temperature	•
Optical interface	•
Highly effective filter system with filter monitoring	•
A wide range of accessories (optional)	•
<b>Connection options</b>	
External dispenser module for liquid cleaning agent	•
<b>Standards / certs / symbols</b>	
Complies with Machinery Directive 2006/42/EC	•
Splash protection IPX1	•
EMC radio suppressed	•
DIN 10512	•
DIN EN 17735	•
ETL	•
NSF	•
ADA	•