

## PDR 910 [EL]

Professional vented dryer, electric heating  
with programmable M Touch Pro controls for the maximum in flexibility.



- Drum volume 6.36 (180.00) ft<sup>3</sup> (l), load size?? – ??
- Unique, gentle fabric care – honeycomb drum
- Precision drying of all fabrics – PerfectDry
- Connected for the future using LAN and Wi-Fi
- Tested for intensive use – unique Miele quality

EAN: 4002516664765 / Material number: 12271740 /  
Old Material Number: 52910017NAM

<b>Construction type and design</b>	
Construction type	Front loader
Product line	Performance Plus
Front	Iron grey
Control panel colour	Stainless steel
Load size with a load ratio of 1:20	20 (9.0) lb (kg)
Drum volume in l	6.36 (180.00) ft <sup>3</sup> (l)
Drying system	Vented system
Door opening [Ø] in in. (mm)	17 3/8 (440)
Door-opening angle in degrees	180
Door hinging	left
Stainless steel honeycomb drum	Yes
<b>Application</b>	
Suitable for hotels and restaurants	•
Suitable for retirement and care homes	•
Suitable for facility management	•
Suitable for dry cleaners	•
Suitable for commercial laundromats	•
Suitable for small businesses	•
Suitable for fire departments and rescue services	•
Suitable for stud farms and stables	•
Suitable for hospitals	•
Suitable for camp sites	•
Suitable for sports clubs	•
Suitable for beauty salons, spas, and fitness centres	•
Suitable for medical and dental practices	•
Suitable for the petrochemical industry	•
Suitable for the food-processing industry	•
Suitable for amusement parks and holiday resorts	•
<b>Performance data</b>	
Specific energy consumption in kWh/kg	0.51
Program duration in minutes	61
<b>Controls</b>	
Control type	M Touch Pro
Programmability	programmable
Program controls	Residual moisture controlled
Max. delay start in h	24
Time left display	•
Program sequence indicator	•
Choice of display language	•
<b>Standard electrical connection</b>	
Heating type	Electric
Electrical connection	208/240 V 60 HZ 2 PH
Electric heater rating in kW	3.70-4.94
Total rated load in kW	4.00-5.20
Fuse rating in A	30
NEMA plug: Twist Lock L6-30	•

## PDR 910 [EL]

Professional vented dryer, electric heating  
with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516664765 / Material number: 12271740 /  
Old Material Number: 52910017NAM

<b>Dimensions and weight of dryer</b>	
External dimensions, net height in in. (mm)	40 3/16 (1020)
External dimensions, net width in in. (mm)	27 9/16 (700)
External dimensions, net depth in in. (mm)	30 1/16 (763)
External dimensions, gross height in in. (mm)	47 7/8 (1215)
External dimensions, gross width in in. (mm)	29 15/16 (760)
External dimensions, gross depth in in. (mm)	32 5/16 (820)
Net weight in lbs. (kg)	159 (72.0)
Gross weight in lbs. (kg)	177 (80)
Maximum floor load in N	853
<b>Emission values</b>	
Emission sound pressure level in the workplace	50 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	3.90
<b>Features</b>	
Intelligent drum reversal	•
Axial airflow	•
Large-surface filter	•
PerfectDry	•
SoftLift drum ribs	•
Low temperature function	•
Communication slot	•
Drum lighting	•
Program selection via colour frame	•
Machine-independent accessories	•
<b>Efficiency and sustainability</b>	
Recycling rate in %	90
<b>Connection options</b>	
Payment system (optional)	•
Optical interface for service access	•
Peak-load negotiation / energy management (optional)	•
Wi-Fi	•
Connector Box	•
LAN module (optional)	•
<b>Capacities</b>	
Breathing masks [number]	4
Protective suits [number]	1
Protective coats [number]	2
Synthetic duvets [number]	1
Synthetic pillows [number]	2
Down comforters [number]	1
Down pillows [number]	2
Cleaning cloths, 22 g [number]	182
Cotton mops, 40 cm [number]	42
Cotton mops, 50 cm [number]	36
Microfibre mops, 40 cm [number]	66
Microfibre mops, 50 cm [number]	47
Horse summer blankets [number]	2

## PDR 910 [EL]

Professional vented dryer, electric heating  
with programmable M Touch Pro controls for the maximum in flexibility.



EAN: 4002516664765 / Material number: 12271740 /  
Old Material Number: 52910017NAM

Standards / certs / symbols	
Splash protection IPX4	•
c ETL US	•
Complies with Machinery Directive 2006/42/EC	•