

## XKM 3200 WL LMD86

Communication module for PLW/PWD 868x or 869x generation machines for ExpertLine for connection to Miele MOVE, Segosoft or other software.

EAN: 4002516866527 / Material number: 12611070 / Old Material Number: 68822104D



- State-of-the-art connection to Miele MOVE
- Secure transmission via Ethernet
- REST interface with data provision in JSON format
- Flexible operation on local networks
- The last 30 process protocols are stored in the machine

<b>Product category</b>	
Glassware Washers, laboratory	•
Thermal disinfectors	•
Washer-disinfectors, medical	•
Washer-disinfectors, fire brigades, and emergency services	•
<b>Machine affiliation</b>	
PLW 8683	•
PLW 8683 CD	•
PLW 8693	•
PLW 8683 [Safety]	•
PLW 8693 [Safety]	•
PWA 8672	•
PWD 8682	•
PWD 8682 C	•
PWD 8682 CD	•
PWD 8692	•
<b>Product category</b>	
Process documentation / operating documentation / communication	•
<b>Application area</b>	
Reprocessing of pipettes / phials	•
Reprocessing of laboratory glassware	•
Reprocessing anaesthetic instruments	•
Reprocessing of MIS instruments	•
Reprocessing of ophthalmology instruments	•
Reprocessing of robotic instruments	•
Reprocessing of GYN instruments	•
Reprocessing of ENT instruments	•
Reprocessing of dental instruments	•
Reprocessing of OR shoes	•
Reprocessing of basins	•
Reprocessing of kidney dishes	•
Reprocessing of baby bottles	•
Reprocessing of surgical instruments	•
Reprocessing of lumened instruments	•
Reprocessing of intramedullary nails / bone marrow drills	•
Reprocessing of trays	•
Reprocessing of mesh trays	•
<b>Product characteristics</b>	
Material	Plastic
Colour	Grey
<b>Dimensions and weight</b>	
External dimensions, net height in in. (mm)	1 5/8 (40)
External dimensions, net width in in. (mm)	3 9/16 (90)
External dimensions, net depth in in. (mm)	4 3/8 (110)
External dimensions, gross height in in. (mm)	4 3/16 (105)
External dimensions, gross width in in. (mm)	6 1/2 (165)
External dimensions, gross depth in in. (mm)	8 5/16 (210)

## XKM 3200 WL LMD86

Communication module for PLW/PWD 868x or 869x generation machines  
for ExpertLine for connection to Miele MOVE, Segosoft or other software.

EAN: 4002516866527 / Material number: 12611070 / Old Material Number: 68822104D



Net weight in lb (kg)	1 (0.18)
Gross weight in lb (kg)	2 (0.46)