

A 500

Mobile unit

With 1 level for cleaning laboratory glassware and utensils.



- For holding inserts and mesh trays
- Extendable to 2 levels with A 603

EAN: 4002516855026 / Material number: 12684430 /
Old Material Number: 69650002D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Large-chamber washer-disinfectors, fire brigades, and emergency services	•
Machine affiliation	
PLW 8615	•
PLW 8615 [Safety]	•
PLW 8616	•
PLW 8616 [Safety]	•
PLW 8617	•
PLW 8617 [Safety]	•
Product category	
Mobile unit for inserts	•
Application area	
Reprocessing of laboratory glassware	•
Product characteristics	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
Capacity	
DIN mesh trays [number]	3
SPRI mesh trays [number]	2
Dimensions and weight	
External dimensions, net height in in. (mm)	6 1/16 (153)
External dimensions, net width in in. (mm)	25 5/8 (650)
External dimensions, net depth in in. (mm)	31 1/8 (790)
External dimensions, gross height in in. (mm)	7 1/2 (190)
External dimensions, gross width in in. (mm)	25 13/16 (655)
External dimensions, gross depth in in. (mm)	31 15/16 (810)
Net weight in lb (kg)	13 (6.02)
Gross weight in lb (kg)	16 (7.37)