

APLW 905

Built-in report printer

retrofitting kit for printing process protocols.



**Image
in progress**

- Thermal printer with 60 mm paper width
- Installed by customer service

EAN: 4002516915027 / Material number: 12685170 / Old Material Number: 69242019D

| Product category | |
|---|---------------|
| SlimLine laboratory glassware washers | • |
| Machine affiliation | |
| PLW 7111 | • |
| PLW 7111 [Safety] | • |
| PWD 7121 | • |
| PWD 7122 | • |
| Product category | |
| Conversion kit | • |
| Process documentation / operating documentation / communication | • |
| Product characteristics | |
| Material | Plastic |
| Colour | Black |
| Application area | |
| Routine monitoring of the cleaning and disinfection process | • |
| Dimensions and weight | |
| External dimensions, gross height in in. (mm) | 5 15/16 (150) |
| External dimensions, gross width in in. (mm) | 13 7/16 (340) |
| External dimensions, gross depth in in. (mm) | 29 9/16 (750) |
| Net weight in lb (kg) | 6 (2.50) |
| Gross weight in lb (kg) | 8 (3.44) |