

SC

Steam condenser

For effective moisture removal from and cooling of exhaust air.



- Only suitable for use in combination with a drying unit
- Can be connected to on-site cooling water circuit

EAN: 4002516855378 / Material number: 12687850 / Old Material Number: 69251301D

| | |
|--|-----------------|
| Product category | |
| Large-capacity washer-disinfectors, laboratory | • |
| Machine affiliation | |
| PLW 8615 | • |
| PLW 8616 | • |
| PLW 8617 | • |
| Product characteristics | |
| Material | Stainless steel |
| Dimensions and weight | |
| External dimensions, gross height in in. (mm) | 24 7/16 (620) |
| External dimensions, gross width in in. (mm) | 15 3/16 (385) |
| External dimensions, gross depth in in. (mm) | 30 3/8 (770) |
| Net weight in lb (kg) | 74 (33.40) |
| Gross weight in lb (kg) | 82 (37.00) |