

WW 45 R  
Laundry tub, red  
with 45 l capacity.



- Suitable for FG 40
- Height (incl. handles) 28.5, width 61, depth 43 cm

EAN: 4002511097605 / Material number: 02084680 / Old Material Number: 59100004D

| Product classification     |   |
|----------------------------|---|
| Washing machines           | • |
| Tumble dryers              | • |
| Ironers                    | • |
| Machine/accessory category |   |
| HM 16-80                   | • |
| HM 16-83                   | • |
| PM 1210                    | • |
| PM 1214                    | • |
| PM 1217                    | • |
| PM 1318                    | • |
| PM 1418                    | • |
| PM 1421                    | • |
| PRI 318                    | • |
| PRI 418                    | • |
| D 500-1750                 | • |
| D 500-2000                 | • |
| D 500-2200                 | • |
| D 500-2500                 | • |
| D 500-3000                 | • |
| D 500-3300                 | • |
| D 600-1750                 | • |
| D 600-2000                 | • |
| D 600-2200                 | • |
| D 600-2500                 | • |
| D 600-3000                 | • |
| D 600-3300                 | • |
| D 800-1300                 | • |
| D 800-1750                 | • |
| D 800-2000                 | • |
| D 800-2200                 | • |
| D 800-2500                 | • |
| D 800-3000                 | • |
| D 800-3300                 | • |
| M 500-1750                 | • |
| M 500-2000                 | • |
| M 500-2200                 | • |
| M 500-2500                 | • |
| M 500-3000                 | • |
| M 500-3300                 | • |
| PM 1621                    | • |
| PM 1625                    | • |
| PM 1630                    | • |
| PM 1635                    | • |
| PM 1825                    | • |
| PM 1830                    | • |
| PM 1835                    | • |
| PT 5135 C                  | • |
| PT 5136                    | • |
| PT 5137 WP                 | • |

WW 45 R  
Laundry tub, red  
with 45 l capacity.



EAN: 4002511097605 / Material number: 02084680 / Old Material Number: 59100004D

|                     |   |
|---------------------|---|
| PT 5140 WP          | • |
| PT 5141 WP          | • |
| PT 5145 C           | • |
| PT 5155 C           | • |
| PT 5156             | • |
| PT 5157 WP          | • |
| PT 5186             | • |
| PT 7186             | • |
| PT 7188             | • |
| PT 7135 C           | • |
| PT 7136             | • |
| PT 7137 WP          | • |
| PT 7138             | • |
| PT 8203             | • |
| PT 8251             | • |
| PT 8251 COP         | • |
| PT 8253             | • |
| PT 8257             | • |
| PT 8257 WP          | • |
| PT 8301             | • |
| PT 8301 COP         | • |
| PT 8303             | • |
| PT 8331             | • |
| PT 8331 COP         | • |
| PT 8333             | • |
| PT 8333 HW          | • |
| PT 8337             | • |
| PT 8337 HW          | • |
| PT 8337 WP          | • |
| PT 8401             | • |
| PT 8403             | • |
| PT 8403 HW          | • |
| PT 8407             | • |
| PT 8407 HW          | • |
| PT 8503             | • |
| PT 8503 HW          | • |
| PT 8507             | • |
| PT 8507 HW          | • |
| PT 8803             | • |
| PT 8803 HW          | • |
| PT 8807             | • |
| PT 8807 HW          | • |
| PT 9136             | • |
| PT 9137 WP          | • |
| PW 413              | • |
| PW 413 Mop Star 130 | • |
| PW 418              | • |
| PW 5064             | • |
| PW 5062             | • |
| PW 5055             | • |
| PW 5065             | • |

WW 45 R  
Laundry tub, red  
with 45 l capacity.

EAN: 4002511097605 / Material number: 02084680 / Old Material Number: 59100004D

|                          |   |
|--------------------------|---|
| PW 5064 MOPSTAR 60       | • |
| PW 5070                  | • |
| PW 5082                  | • |
| PW 5084 MOPSTAR 80       | • |
| PW 5104 MOPSTAR 100      | • |
| PW 5105 Vario            | • |
| PW 5134 MOPSTAR 130      | • |
| PW 6055                  | • |
| PW 6065                  | • |
| PW 6055 Vario            | • |
| PW 6065 Vario            | • |
| PW 6065 Plus             | • |
| PW 6068 Plus             | • |
| PW 6080                  | • |
| PW 6088                  | • |
| PW 6107                  | • |
| PW 6137                  | • |
| PW 5136                  | • |
| PW 6163                  | • |
| PW 6167                  | • |
| PW 6207                  | • |
| PW 6241                  | • |
| PW 6243                  | • |
| PW 6321                  | • |
| PW 6323                  | • |
| PW 811                   | • |
| PW 814                   | • |
| PW 818                   | • |
| PW 9055                  | • |
| PW 9065                  | • |
| PWT 6089                 | • |
| PWM 500-08               | • |
| PWM 500-09               | • |
| PWM 506 Mop Star 60      | • |
| PWM 507                  | • |
| PWM 508 Mop Star 80      | • |
| PWM 900-09               | • |
| PWM 906                  | • |
| PWM 907                  | • |
| PWM 908                  | • |
| PW 200 Profi@Work        | • |
| PT 200 Profi@Work        | • |
| PDR 300 SmartBiz         | • |
| PWM 300 SmartBiz         | • |
| PDR 500-08               | • |
| PDR 507                  | • |
| PDR 900-08               | • |
| PDR 908                  | • |
| PIB 100                  | • |
| <b>Product category</b>  |   |
| Storage/transport system | • |

WW 45 R  
Laundry tub, red  
with 45 l capacity.



EAN: 4002511097605 / Material number: 02084680 / Old Material Number: 59100004D

| <b>Product properties</b>               |         |
|---|---------|
| Electrical connection                   | OHNE    |
| Material                                | Plastic |
| Colour                                  | Red     |
| Volume in l                             | 45      |
| <b>Dimensions and weight</b>            |         |
| External dimensions, net height in mm   | 285     |
| External dimensions, net width in mm    | 610     |
| External dimensions, net depth in mm    | 430     |
| External dimensions, gross height in mm | 290     |
| External dimensions, gross width in mm  | 610     |
| External dimensions, gross depth in mm  | 430     |
| Net weight [kg]                         | 2,00    |
| Gross weight in kg                      | 2,00    |