

FBW

Aluminium trolley

With vertically adjustable base for uniform handle height.



- Capacity: 380 l Litres
- 2 swivel castors with brakes
- Height 86, width 106, depth 71 cm

EAN: 4002511097674 / Material number: 03049680 / Old Material Number: 59110006D

Product classification	
Washing machines	•
Tumble dryers	•
Ironers	•
Machine/accessory category	
HM 16-80	•
HM 16-83	•
PM 1210	•
PM 1214	•
PM 1217	•
PM 1318	•
PM 1418	•
PM 1421	•
D 500-2000	•
D 500-2200	•
D 500-2500	•
D 500-3000	•
D 500-3300	•
D 600-1750	•
D 600-2000	•
D 600-2200	•
D 600-2500	•
D 600-3000	•
D 600-3300	•
D 800-1300	•
D 800-1750	•
D 800-2000	•
D 800-2200	•
D 800-2500	•
D 800-3000	•
D 800-3300	•
M 500-1750	•
M 500-2000	•
M 500-2200	•
M 500-2500	•
M 500-3000	•
M 500-3300	•
PM 1621	•
PM 1625	•
PM 1630	•
PM 1635	•
PM 1825	•
PM 1830	•
PM 1835	•
PT 5135 C	•
PT 5136	•
PT 5137 WP	•
PT 5140 WP	•
PT 5145 C	•
PT 5186	•

FBW

Aluminium trolley

With vertically adjustable base for uniform handle height.



EAN: 4002511097674 / Material number: 03049680 / Old Material Number: 59110006D

PT 7186	•
PT 7188	•
PT 7135 C	•
PT 7136	•
PT 7137 WP	•
PT 8203	•
PT 8251	•
PT 8251 COP	•
PT 8253	•
PT 8257	•
PT 8257 WP	•
PT 8301	•
PT 8301 COP	•
PT 8303	•
PT 8331	•
PT 8331 COP	•
PT 8333	•
PT 8333 HW	•
PT 8337	•
PT 8337 HW	•
PT 8337 WP	•
PT 8401	•
PT 8403	•
PT 8403 HW	•
PT 8407	•
PT 8407 HW	•
PT 8503	•
PT 8503 HW	•
PT 8507	•
PT 8507 HW	•
PT 8803	•
PT 8803 HW	•
PT 8807	•
PT 8807 HW	•
PW 413	•
PW 418	•
PW 5064	•
PW 5062	•
PW 5065	•
PW 5064 MOPSTAR 60	•
PW 5070	•
PW 5082	•
PW 5084 MOPSTAR 80	•
PW 5104 MOPSTAR 100	•
PW 5105 Vario	•
PW 5134 MOPSTAR 130	•
PW 6055	•
PW 6065	•
PW 6055 Vario	•
PW 6065 Vario	•
PW 6065 Plus	•

FBW

Aluminium trolley

With vertically adjustable base for uniform handle height.



EAN: 4002511097674 / Material number: 03049680 / Old Material Number: 59110006D

PW 6068 Plus	•
PW 6080	•
PW 6088	•
PW 6107	•
PW 6137	•
PW 5136	•
PW 6163	•
PW 6167	•
PW 6207	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
PWT 6089	•
PW 200 Profi@Work	•
PT 200 Profi@Work	•
<b>Product category</b>	
Storage/transport system	•
<b>Product properties</b>	
Electrical connection	OHNE
Material	Aluminium
Volume in l	380
<b>Dimensions and weight</b>	
External dimensions, net height in mm	860
External dimensions, net width in mm	1060
External dimensions, net depth in mm	710
External dimensions, gross height in mm	860
External dimensions, gross width in mm	1060
External dimensions, gross depth in mm	710
Net weight [kg]	25,00
Gross weight in kg	25,00