

SW

Laundry bag trolley

Foldable for storage in the smallest of spaces.



- Tubular structure with detachable sheet holders
- Solid rubber tyres with four lockable swivel castors
- Height 81, width 90, depth 58 cm

EAN: 4002511097759 / Material number: 03049800 / Old Material Number: 59110015D

Product classification	
Washing machines	•
Tumble dryers	•
Ironers	•
Machine/accessory category	
HM 16-80	•
HM 16-83	•
PM 1210	•
PM 1214	•
PM 1217	•
PM 1318	•
PM 1418	•
PM 1421	•
D 500-2000	•
D 500-2200	•
D 500-2500	•
D 500-3000	•
D 500-3300	•
D 600-1750	•
D 600-2000	•
D 600-2200	•
D 600-2500	•
D 600-3000	•
D 600-3300	•
D 800-1300	•
D 800-1750	•
D 800-2000	•
D 800-2200	•
D 800-2500	•
D 800-3000	•
D 800-3300	•
M 500-1750	•
M 500-2000	•
M 500-2200	•
M 500-2500	•
M 500-3000	•
M 500-3300	•
PM 1621	•
PM 1625	•
PM 1630	•
PM 1635	•
PM 1825	•
PM 1830	•
PM 1835	•
PT 5135 C	•
PT 5136	•
PT 5137 WP	•
PT 5140 WP	•
PT 5145 C	•
PT 5186	•

SW

Laundry bag trolley

Foldable for storage in the smallest of spaces.



EAN: 4002511097759 / Material number: 03049800 / Old Material Number: 59110015D

PT 7186	•
PT 7188	•
PT 7135 C	•
PT 7136	•
PT 7137 WP	•
PT 8203	•
PT 8251	•
PT 8251 COP	•
PT 8253	•
PT 8257	•
PT 8257 WP	•
PT 8301	•
PT 8301 COP	•
PT 8303	•
PT 8331	•
PT 8331 COP	•
PT 8333	•
PT 8333 HW	•
PT 8337	•
PT 8337 HW	•
PT 8337 WP	•
PT 8401	•
PT 8403	•
PT 8403 HW	•
PT 8407	•
PT 8407 HW	•
PT 8503	•
PT 8503 HW	•
PT 8507	•
PT 8507 HW	•
PT 8803	•
PT 8803 HW	•
PT 8807	•
PT 8807 HW	•
PW 413	•
PW 418	•
PW 5064	•
PW 5062	•
PW 5065	•
PW 5064 MOPSTAR 60	•
PW 5070	•
PW 5082	•
PW 5084 MOPSTAR 80	•
PW 5104 MOPSTAR 100	•
PW 5105 Vario	•
PW 5134 MOPSTAR 130	•
PW 6055	•
PW 6065	•
PW 6055 Vario	•
PW 6065 Vario	•
PW 6065 Plus	•

SW

Laundry bag trolley

Foldable for storage in the smallest of spaces.



EAN: 4002511097759 / Material number: 03049800 / Old Material Number: 59110015D

PW 6068 Plus	•
PW 6080	•
PW 6088	•
PW 6107	•
PW 6137	•
PW 5136	•
PW 6163	•
PW 6167	•
PW 6207	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
PWT 6089	•
PW 200 Profi@Work	•
PT 200 Profi@Work	•
<b>Product category</b>	
Storage/transport system	•
<b>Product properties</b>	
Electrical connection	OHNE
<b>Dimensions and weight</b>	
External dimensions, net height in mm	1150
External dimensions, net width in mm	210
External dimensions, net depth in mm	560
External dimensions, gross height in mm	1170
External dimensions, gross width in mm	230
External dimensions, gross depth in mm	590
Net weight [kg]	8,00
Gross weight in kg	9,00