

E 135/3

Insert

for optimum loading of 19 baby bottles up to 120 ml.



- Suitable for 19 baby bottles x 120 ml
- Suitable for bottles sized 56 x 56 mm, neck: 49 x 49 mm
- For upper basket A 102 and lower basket A 151

EAN: 4002511115934 / Material number: 03808670 / Old Material Number: 69513504D

|   |                 |
|---|-----------------|
| <b>Product category</b>                     |                 |
| Washer-disinfectors, medical                | •               |
| Large-capacity washer-disinfectors, medical | •               |
| <b>Machine affiliation</b>                  |                 |
| G 7823                                      | •               |
| G 7824                                      | •               |
| G 7826                                      | •               |
| PG 8528                                     | •               |
| PG 8535                                     | •               |
| PG 8536                                     | •               |
| PG 8562                                     | •               |
| PG 8582                                     | •               |
| PG 8582 CD                                  | •               |
| PG 8592                                     | •               |
| <b>Product category</b>                     |                 |
| Insert for various flasks                   | •               |
| <b>Product properties</b>                   |                 |
| Material                                    | Stainless steel |
| Colour                                      | Stainless Steel |
| <b>Area of application</b>                  |                 |
| Reprocessing of baby bottles                | •               |
| <b>Capacity</b>                             |                 |
| Baby bottles [number]                       | 19              |
| <b>Standard electrical connection</b>       |                 |
| Number of phases                            | 0               |
| Voltage in V                                | 0               |
| Frequency in Hz                             | 0               |
| Total rated load in kW                      | 0,00            |
| Fuse rating in A                            | 0               |
| <b>Dimensions and weight</b>                |                 |
| External dimensions, net height in mm       | 135             |
| External dimensions, net width in mm        | 192             |
| External dimensions, net depth in mm        | 447             |
| External dimensions, gross height in mm     | 470             |
| External dimensions, gross width in mm      | 130             |
| External dimensions, gross depth in mm      | 230             |
| Net weight in kg                            | 1,94            |
| Gross weight in kg                          | 2,00            |