


E 205

Use

For the optimum loading of glasses.



- Suitable for lower basket U 890
- For 17 glasses with a diameter of 6.6 cm
- With perforated tray inlay to interrupt the water jet
- Rail height 220 mm
- The maximum vertical clearance with glasses is 270 mm


EAN: 4002511808874 / Material number: 03808980 / Old Material Number: 67520501D

Product classification	
Fresh-water dishwashers	•
Machine affiliation	
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
Product category	
Insert for glassware	•
Product properties	
Material	Wire, rilsan-coated
Colour	White
Number of rows	2
Rail height in mm	220
Maximum vertical clearance in mm	270
For use in lower basket	APFD 220, U 890
Capacity	
Glasses up to max. Ø 66 mm [number]	17
Standard electrical connection	
Number of phases	0
Voltage in V	0

E 205

Use

For the optimum loading of glasses.



EAN: 4002511808874 / Material number: 03808980 / Old Material Number: 67520501D

Frequency in Hz	0
Total rated load in kW	0,00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	221
External dimensions, net width in mm	243
External dimensions, net depth in mm	494
External dimensions, gross height in mm	230
External dimensions, gross width in mm	505
External dimensions, gross depth in mm	250
Net weight in kg	1,40
Gross weight in kg	1,80