

E 313

Wall fitting

for the manual production of demineralised water.



- Pressurised to 10 bar
- Complete with pressure hose 150 cm

EAN: 4002511115279 / Material number: 03830330 / Old Material Number: 69431301D

Product category	
Fresh-water dishwashers	•
Tank dishwashers	•
Throughfeed tank dishwashers	•
Washer-disinfectors, laboratory	•
Machine affiliation	
G 8066	•
PG 8067	•
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8063	•
PG 8164	•
PG 8165	•
PG 8166	•
PG 8169	•
PG 8172	•
PG 8172 Eco	•
PTD 901	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
PTD 701	•

E 313

Wall fitting

for the manual production of demineralised water.



EAN: 4002511115279 / Material number: 03830330 / Old Material Number: 69431301D

PTD 702	•
PTD 703	•
PTD 704	•
PG 8535	•
PG 8536	•
<b>Product category</b>	
Water treatment	•
<b>Product properties</b>	
Material	Plastic
Colour	Black
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0,00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	0
External dimensions, net width in mm	0
External dimensions, net depth in mm	0
External dimensions, gross height in mm	195
External dimensions, gross width in mm	190
External dimensions, gross depth in mm	240
Net weight in kg	1,06
Gross weight in kg	1,31