

E 459

Use

For the optimum loading of glasses.



- Suitable for upper basket carrier O 898 and lower basket U 876
- For 12 glasses with a diameter of max. 7 cm
- Max. glass height 22 cm
- With perforated tray inlay to optimise the water jet

EAN: 4002511958197 / Material number: 04326630 / Old Material Number: 67545901D

Product classification	
Fresh-water dishwashers	•
Machine affiliation	
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
Product category	
Insert for glassware	•
Product properties	
Material	Stainless steel
Colour	Stainless Steel
For use in upper basket	O 898
For use in lower basket	U 876
Capacity	
Glasses up to max. Ø 70 mm [number]	12
Standard electrical connection	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0,00

E 459

Use

For the optimum loading of glasses.



EAN: 4002511958197 / Material number: 04326630 / Old Material Number: 67545901D

Fuse rating in A

0

**Dimensions and weight**

External dimensions, net height in mm

170

External dimensions, net width in mm

200

External dimensions, net depth in mm

460

External dimensions, gross height in mm

185

External dimensions, gross width in mm

240

External dimensions, gross depth in mm

485

Net weight in kg

1,37

Gross weight in kg

1,63