

E 888

Use

For the optimum loading of plates.



- Suitable for lower basket U 890
- For 18 plates with a diameter of max. 30 cm
- Rail height 175 mm, distance between rails 30 mm

EAN: 4002512259682 / Material number: 05018690 / Old Material Number: 67588801D

<b>Product category</b>	
Fresh-water dishwashers	•
<b>Machine affiliation</b>	
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8061	•
PG 8061 U	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
PFD 408 U	•
<b>Product category</b>	
Insert for plates	•
<b>Product properties</b>	
Material	Wire, rilsan-coated
Colour	White
Distance between rails in mm	30
Rail height in mm	175
For use in lower basket	U 890
<b>Capacity</b>	
Plates up to Ø 300 mm [number]	18
Plates up to Ø 350 mm [number]	9
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0

E 888

Use

For the optimum loading of plates.



EAN: 4002512259682 / Material number: 05018690 / Old Material Number: 67588801D

Frequency in Hz	0
Total rated load in kW	0,00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	175
External dimensions, net width in mm	460
External dimensions, net depth in mm	460
External dimensions, gross height in mm	205
External dimensions, gross width in mm	520
External dimensions, gross depth in mm	535
Net weight in kg	1,00
Gross weight in kg	2,17