

## DOS-G2

Pump casing in stainless steel

With space for a maximum of 3 pumps P2 for dispensing liquid media.



- 12-pole terminal strip for easy connection

EAN: 4002512614870 / Material number: 05572530 / Old Material Number: 59170079D

<b>Product category</b>	
Washing machines	•
<b>Machine/accessory category</b>	
PW 413	•
PW 413 Mop Star 130	•
PW 418	•
PW 5134 MOPSTAR 130	•
PW 6107	•
PW 6137	•
PW 5136	•
PW 6163	•
PW 6167	•
PW 6207	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 811	•
PW 814	•
PW 818	•
PWM 500-08	•
PWM 500-09	•
PWM 506 Mop Star 60	•
PWM 507	•
PWM 508 Mop Star 80	•
PWM 509	•
PWM 900-09	•
PWM 906	•
PWM 907	•
PWM 908	•
PWM 511	•
PWM 909	•
PWM 514	•
PWM 520	•
PWM 912	•
PWM 916	•
PWM 920	•
PDW 909	•
<b>Product category</b>	
Dispenser system	•
<b>Product properties</b>	
Electrical connection	OHNE
Material	Stainless steel
Colour	Stainless Steel
<b>Dimensions and weight</b>	
External dimensions, net height in mm	540
External dimensions, net width in mm	540
External dimensions, net depth in mm	190
External dimensions, gross height in mm	185
External dimensions, gross width in mm	540
External dimensions, gross depth in mm	540

DOS-G2

Pump casing in stainless steel

With space for a maximum of 3 pumps P2 for dispensing liquid media.

EAN: 4002512614870 / Material number: 05572530 / Old Material Number: 59170079D



Net weight [kg]	2,30
Gross weight in kg	2,50