

E 908/1

Insert

For separable MIS instruments/work inserts or fibre optics.



- Mesh width 8 x 1 mm (base), sides enclosed
- Interior sections individually adjustable with 4 bars
- Hook for hanging in E 906/1

EAN: 4002513252286 / Material number: 05704010 / Old Material Number: 69590802D

<b>Product category</b>	
Washer-disinfectors, medical	•
<b>Machine affiliation</b>	
PG 8536	•
<b>Product category</b>	
Insert/module for MIS instruments	•
<b>Product properties</b>	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
<b>Area of application</b>	
Reprocessing of MIS instruments	•
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0,00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	130
External dimensions, net width in mm	460
External dimensions, net depth in mm	36
External dimensions, gross height in mm	150
External dimensions, gross width in mm	505
External dimensions, gross depth in mm	100
Net weight in kg	0,68
Gross weight in kg	0,85