

DOS-G2

Pump casing in stainless steel

With space for a maximum of 3 pumps P2 for dispensing liquid media.



- 12-pole terminal strip for easy connection

EAN: 4002513310610 / Material number: 05760630 / Old Material Number: 59170112USA

Product category	
Washing machines	•
Machine/accessory category	
PW 413	•
PW 418	•
PW 5134 MOPSTAR 130	•
PW 6107	•
PW 6137	•
PW 5136	•
PW 6163	•
PW 6167	•
PW 6207	•
PW 6241	•
PW 6243	•
PW 6321	•
PW 6323	•
PW 811	•
PW 814	•
PW 818	•
Product category	
Dispenser system	•
Product properties	
Electrical connection	OHNE
Dimensions and weight	
External dimensions, net height in mm	540
External dimensions, net width in mm	540
External dimensions, net depth in mm	190
External dimensions, gross height in mm	185
External dimensions, gross width in mm	540
External dimensions, gross depth in mm	540
Net weight [kg]	2,30
Gross weight in kg	2,50