

E 474/4

Basic mobile unit

for optimum loading of up to 2 MIS sets in a modular system.



- For hollow instruments in 3 insert modules
- Equipped with connection for hot air drying
- For: E 903, E 905, E 906, E 444, E 460, E 457, E 142
- Bracket for ML/2 for mobile unit recognition / spray arm control

EAN: 4002513805536 / Material number: 06439160 / Old Material Number: 69547405D

<b>Product category</b>	
Washer-disinfectors, medical	•
<b>Machine affiliation</b>	
PG 8536	•
<b>Product category</b>	
Mobile unit for MIS instruments	•
<b>Product properties</b>	
Material	Stainless steel
Colour	Stainless Steel
<b>Area of application</b>	
Reprocessing of MIS instruments	•
Reprocessing of dental instruments	•
<b>Capacity</b>	
MIS sets [number]	2
<b>Standard electrical connection</b>	
Number of phases	0
Voltage in V	0
Frequency in Hz	0
Total rated load in kW	0,00
Fuse rating in A	0
<b>Dimensions and weight</b>	
External dimensions, net height in mm	507
External dimensions, net width in mm	535
External dimensions, net depth in mm	515
External dimensions, gross height in mm	540
External dimensions, gross width in mm	540
External dimensions, gross depth in mm	630
Net weight in kg	10,17
Gross weight in kg	10,17
<b>Companion pack</b>	
E 362 blind stopper [number]	2
E 447 female adapter, for male Luer Lock [number]	3