


E 950/1

Mobile unit

for the optimum loading of narrow necked glassware on 3 levels.



- Equipped with 232 nozzles
- Levels 1+3: Each 80 nozzles ID 90 (2.5 x 90 mm)
- Level 2: 72 nozzles ID 90 (2.5 x 90 mm)
- Maximum vertical clearance on all three levels 148 mm each

EAN: 4002514072708 / Material number: 06696990 / Old Material Number: 69595002D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Machine affiliation	
PG 8527	•
Product category	
Mobile unit for narrow-necked glassware	•
Product properties	
Material	Stainless steel, Plastic
Colour	Stainless Steel, Black
Area of application	
Reprocessing of laboratory glassware	•
Capacity	
Narrow-necked glassware [number]	232
Standard electrical connection	
Number of phases	0
Voltage in V	0-0
Frequency in Hz	0-0
Total rated load in kW	0,00-0,00
Fuse rating in A	0-0
Dimensions and weight	
External dimensions, net height in mm	572
External dimensions, net width in mm	640
External dimensions, net depth in mm	790
External dimensions, gross height in mm	650
External dimensions, gross width in mm	650
External dimensions, gross depth in mm	820
Net weight in kg	28,20
Gross weight in kg	40,00
Companion pack	
Magnetic strip for automatic mobile unit recognition (incl. magnets) [number]	1