

Printer  
Report printer  
for process documentation, integrated



- 8-wire matrix printer for process documentation
- Report creation and printing can be configured
- Can be installed on the operator side of the PG 8527
- Can be installed on the clean or unclean side of the PG 8528

EAN: 4002514111766 / Material number: 06758340 / Old Material Number: 69247001D

Product category	
Large-capacity washer-disinfectors, laboratory	•
Large-capacity washer-disinfectors, medical	•
Machine affiliation	
PG 8527	•
PG 8528	•
Product category	
Other accessories	•
Standard electrical connection	
Number of phases	1
Neutral conductor	N
AC/DC	AC
Voltage in V	220-240
Frequency in Hz	50-60
Total rated load in kW	0,00-0,00
Fuse rating in A	0-0
Dimensions and weight	
External dimensions, gross height in mm	305
External dimensions, gross width in mm	300
External dimensions, gross depth in mm	200
Net weight in kg	0,90
Gross weight in kg	1,00