

B 995 D

Rotary ironer

with steam function for optimum results and even more convenience.



- No physical effort required thanks to high pressure
- Convenient ironing of large laundry pieces – wide heater plate
- Individual work speed thanks to variable roller speed
- Iron difficult laundry items easily – all-round free roller end
- Best result even with dry textiles – Steam function

EAN: 4002514443706 / Material number: 07222770 / Old Material Number: 13099506GB

Design	
Colour	Lotus white
Perfect ironing results	
Temperature selection to suit textiles	•
High contact pressure (N/cm ²)	0,35
Laundry feed board for easy laundry feed	•
Convenient infeed board with ample storage space	•
Airing bar for crease-free cooling	•
Steam function	•
Steam generator capacity in l	0,84
Dual-tank technology	•
Uses tap water	•
Time-saving ironing	
Roller length in mm	830
Variable roller speed	•
Moisture-absorbing roller padding	•
User convenience	
Effortless ironing while seated possible	•
Free roller end	•
Clear control panel	•
Convenient folding mechanism	•
Easily manoeuvrable thanks to four castors	•
Safety	
Automatic finger guard	•
Emergency release	•
Good stability	•
Technical data	
Dimensions in mm (width)	985
Dimensions in mm (height)	959
Dimensions in mm (depth)	380
Dimensions in mm (width), folded	500
Dimensions in mm (height), folded	1055
Dimensions in mm (depth), folded	380
Total rated load in kW	3,00
Frequency in Hz	50-60
Accessories supplied	
Adhesive film for temperature selector	•
Funnel for water container	•