

## HM16-80 D [EL]

Rotary ironer, electrically heated

with steam function for optimum results and maximum convenience.



- Performance 13.0 kg/h\*, roller diameter 160 mm, working width 830 mm
- Iron comfortably while seated
- Work at your own pace thanks to variable roller speed
- Durable roller padding – aramid needle felt cloth
- Easy to store – fold-away function

\* With 20 % residual moisture – performance data according to DIN 11902: the achievable ironing performance depends on overall conditions such as, for example, the type of laundry and the experience of the operator.

EAN: 4002514581781 / Material number: 07362940 / Old Material Number: 53168001D

Construction type and version	
Construction type	Laundry infeed and outfeed at the front
Can be set up against a wall	•
Range	Professional
Outer casing	Lotus white
Roller diameter in mm	160
Working width in mm	830
Heater plate material	Aluminium
Padding	Polyester needle-felt cloth
Ironer cover	ARAMID needle-felt cloth
Application	
Suitable for the hotel and catering industry	•
Suitable for retirement and care homes	•
Suitable for residential homes and apartments	•
Suitable for commercial laundries	•
Suitable for offshore use	•
Suitable for marine use	•
Suitable for camp sites	•
Suitable for domestic use	•
Performance data	
Max. ironing performance at 20 % residual moisture in kg/h	13,0
Tested operating hours	2500
Control system	
Control system	Rotary control
Touch display (optional)	Drehwahlschalter
Minimum ironing speed, controlled in m/min	2,0
Maximum ironing speed, controlled in m/min	4,5
Adjustable temperature	In temperature stages
Standard electrical connection	
Heating type	Electric
Electrical connection	AC 220-240V 50-60HZ
Electric heater rating in kW	3,10-3,70
Boiler heater rating in kW	0,85
Total connected load in kW	3,20-3,80
Fuse rating in A	16
Dimensions and weight	
External dimensions, height in mm	959
External dimensions, width in mm	985
External dimensions, depth in mm	380
External dimensions, gross height in mm	570
External dimensions, gross width in mm	1120
External dimensions, gross depth in mm	450
Net weight in kg	39
Gross weight in kg	45
Maximum floor load in N/m <sup>2</sup>	382
Features	
Steam function	•
Free roller end	•
Fold-away function	•

HM16-80 D [EL]

Rotary ironer, electrically heated

with steam function for optimum results and maximum convenience.



EAN: 4002514581781 / Material number: 07362940 / Old Material Number: 53168001D

Automatic finger guard	•
Foot switch	•
Airing bar	•
4 castors gentle on the floor	•
Feed-in board	•
Laundry return feed	•
Option of ironing when seated	•
Machine-independent accessories	•
<b>Standards, test certificates and symbols</b>	
VDE	•
CE	•
WEEE	•
VDE-EMC	•
Complies with Machinery Directive 2006/42/EC	•