

KF 1901 Vi

MasterCool fridge-freezer

with maximum storage space and high-quality features for exacting demands.



- Gentle storage and maximum enjoyment – MasterFresh
- No icing up of food and no need to defrost thanks to Frost free
- Store food anywhere in the refrigerator – DynaCool
- Perfect illumination thanks to halogen emitters – BrilliantLight
- Infinitely height-adjustable internal containers – Drop and Lock

EAN: 4002514652511 / Material number: 07514940 / Old Material Number: 38190101GB

Appliance category	
Fridge-freezer	•
Construction type	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Side-by-side enabled	•
Design	
Refrigeration section lighting	BrilliantLight
User convenience	
Freshness system	MasterFresh
DynaCool	•
NoFrost	•
DuplexCool	•
Ice cube maker with mains water connection (IceMaker)	•
Control system	
Operating concept	TouchControl
Fridge compartment can be switched off	Yes
Independent temperature regulation of fridge and freezer zones	Yes
SuperCool	•
SuperFreeze	•
No. of temperature zones	2
Fridge/Fridge section	
No. of shelves	3
No. of crisper drawers	1
Number of inner door racks for tinned food	2
Door rack for bottles	1
Freezer/Freezer section	
Number of freezer drawers	2
Safety	
Acoustic door alarm	•
Acoustic temperature alarm	•
Optical door alarm	•
Optical temperature alarm	•
Technical data	
Niche width in mm min.	915
Niche width in mm max.	918
Niche height in mm min.	2134
Niche height in mm max.	2164
Niche depth in mm	629
Appliance width in mm	908
Appliance height in mm	2127
Appliance depth in mm	610
Weight in kg	231,0
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	38
Max. door front weight – freezer, in kg	14

KF 1901 Vi

MasterCool fridge-freezer

with maximum storage space and high-quality features for exacting demands.




EAN: 4002514652511 / Material number: 07514940 / Old Material Number: 38190101GB

Climate class	SN-T
including PerfectFresh zone in l	70
Total usable capacity in l	488
Storage time in case of fault in h	17
Current consumption (mA)	2300
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2,2
Accessories included	
Ice cube tray	•

KF 1901 Vi


MasterCool fridge-freezer

with maximum storage space and high-quality features for exacting demands.




Side by side assembly, MasterCool (footnote) (installation drawings)

1. side wall heater




KF1801Vi, KF1811Vi, KF1901Vi, KF1911Vi, dimensions of appliance, MasterCool (Sketch) *Footnote


KF1801Vi / KF1811Vi: A = 762 mm, KF1901Vi / KF1911Vi: A = 915 mm



ventilation area of niche, MasterCool (Sketch)




Side by side assembly, MasterCool (Sketch)



Opening angel 90°/115°, right side stop, MasterCool (Sketch) *footnote

A) Appliance door width, K 2601 Vi, K 2601 SF, KWT 2601 Vi, KWT 2601 SF, KWT 2661 ViS, KWT 2661 SFS: 677 mm (26 2/3 , inch);, K 2602 Vi, K 2602 SF, KWT 2602 Vi, KWT 2602 SF, KWT 2662 ViS, KWT 2662 SFS: 677 mm (26 2/3 , inch);, K 2801 Vi, K 2801 SF, KF 2801 Vi, KF 2801 SF: 829 mm (32 2/3 inch);, K 2802 Vi, K 2802 SF, KF 2802 Vi, KF 2802 SF: 829 mm (32 2/3 inch);, K 2901 Vi, K 2901 SF, KF 2901 Vi, KF 2901 SF: 982 mm (38 2/3 inch);, K 2902 Vi, K 2902 SF, KF 2902 Vi, KF 2902 SF: 982 mm (38 2/3 inch);, B) Furniture front (max. 38 mm) (1 1/2 inch), C) Door handle, D) Distance door to wall (without furniture front and door handle):, K 2601 Vi, K 2601 SF, KWT 2601 Vi, KWT 2601 SF, KWT 2661 ViS, KWT 2661 SFS: 296 mm (11 2/3 , inch);, K 2602 Vi, K 2602 SF, KWT 2602 Vi, KWT 2602 SF, KWT 2662 ViS, KWT 2662 SFS: 296 mm (11 2/3 , inch);, K 2801 Vi, K 2801 SF, KF 2801 Vi, KF 2801 SF: 363 mm (14 1/3 inch);, K 2802 Vi, K 2802 SF, KF 2802 Vi, KF 2802 SF: 363 mm (14 1/3 inch);, K 2901 Vi, K 2901 SF, KF 2901 Vi, KF 2901 SF: 428 mm (16 7/8 inch);, K 2902 Vi, K 2902 SF, KF 2902 Vi, KF 2902 SF: 428 mm (16 7/8 inch), E) ONLY valid for SF versions: A + 25 mm (1 inch)




K1801Vi, K1901Vi, KF1801Vi, KF1901Vi, F1411Vi, F1811Vi, F1911Vi, securing fixing frame, MasterCool (Sketch) *Footnote

- Mark gap X on the inside of the furniture front., - Similarly, locate and mark the midpoint Y on the furniture front., - Remove the fixing frame from the appliance door and position it according to the markings on the furniture front., - Pre-drill the holes., - Screw the fixing frame to the furniture front, using at least one screw for each fixing point., - Secure the fixing frame to the top of the furniture front, using at least 10 screws.

KF 1901 Vi


MasterCool fridge-freezer

with maximum storage space and high-quality features for exacting demands.




K1801Vi, K1901Vi, F1811Vi, F1911Vi, KF1801Vi, KF1901, securing fixing frame, MasterCool (Sketch) *Footnote


- Mark gap X on the inside of the furniture front, - Remove the fixing frame from the appliance door and position it according to the markings on the furniture front, - Pre-drill the holes, - Screw the fixing frame to the furniture front, using at least one screw for each fixing point, - Secure the fixing frame to the top of the furniture front, using at least 10 screws.



K1801Vi, K1901Vi, F1411Vi, F1811Vi, F1911Vi, KF1801Vi, KF1901Vi, inserting angle trims, MasterCool (Sketch)




laying cabling and pipework, MasterCool (installation drawings)




Opening angle 115°, MasterCool (Sketch) with footnote

A) Appliance door width, K 1801 Vi, KF 1801 Vi: 829 mm, K 1901 Vi, KF 1901 Vi: 982 mm, KWT 1601 Vi: 677 mm, KWT 1602 Vi: 677 mm, B) Furniture front (max. 38 mm), C) Door handle, D) Distance between appliance door and the wall (excluding furniture front and door handle), K 1801 Vi, KF 1801 Vi: 363 mm, K 1901 Vi, KF 1901 Vi: 428 mm, KWT 1601 Vi: 299 mm



Side-by-side, MasterCool, with partition wall, with heating mat (Sketch) (with footnote)

1) Heating mat



Side-by-side, MasterCool, without partition wall, with heating mat (Sketch) (with footnote)

1) Heating mat KSK 2001 (EU, AUS, CN) or KSK 2002 (US, CA, MX, BR)