

CS 1327 Y  
ProLine element  
with electrically heated Tepan Yaki




- Professional design – Stainless steel surface, 380 mm wide
- Particularly versatile – 2 separately controlled heating areas
- Particularly versatile – fry, grill, braise, sauté, etc.
- Easy and direct controls -operation via metal rotary dial control
- Very convenient, safe – operating and residual heat indicator

EAN: 4002514994871 / Material number: 07967210 / Old Material Number: 27132750D

|  |                       |
|--|-----------------------|
| <b>Heating type</b>  |                       |
| Heating type   | Other type of heating |
| <b>Construction type</b>   |                       |
| ProLine  | •                     |
| <b>Design</b>  |                       |
| Stainless-steel frame  | •                     |
| Surface-mounted installation                                       | •                     |
| Surface-mounted/flush-fit  | –/–                   |
| Stainless steel Tepan surface                                      | •                     |
| <b>Cooking zone details</b>  |                       |
| Number of cooking zones/cooking areas                              | –/–                   |
| <b>1st cooking zone/cooking area</b>                               |                       |
| Position   | In front              |
| Type   | Tepan area            |
| Size in mm   | Ø 190 / 190x290       |
| Max. rating in W   | 1200                  |
| <b>2nd cooking zone/cooking area</b>                               |                       |
| Position   | Rear                  |
| Type   | Tepan area            |
| Size in mm   | Ø 190 / 190x290       |
| Max. rating in W   | 1200                  |
| <b>User convenience</b>  |                       |
| Operation via knobs  | •                     |
| <b>Safety</b>  |                       |
| Residual heat indicator  | •                     |
| <b>Technical data</b>  |                       |
| Dimensions (H x W x D) in mm                                       | 118 x 380 x 520       |
| Dimensions in mm (width)   | 380                   |
| Dimensions in mm (height)  | 118                   |
| Dimensions in mm (depth)   | 520                   |
| Cut-out dimensions (W x D) with surface-mounted installation in mm | 364 mm x 500 mm       |
| Cutout dimensions in mm (width) with surface-mounted installation  | 364 mm                |
| Cutout dimensions in mm (depth) with surface-mounted installation  | 500 mm                |
| Weight in kg   | 10                    |
| Total rated load in kW   | 2,40-2,60             |
| Length of supply lead in m   | 2,0                   |
| Voltage in V   | 230-240               |
| Frequency in Hz  | 50-60                 |
| <b>Accessories included</b>  |                       |
| Mains cable  | Yes                   |

CS 1327 Y  
ProLine element  
with electrically heated Tepan Yaki



CS 1327 Y (Installation drawing)

1) Front, 2) Height for building in, 3) Mains connection box  
with cable, 2000 mm long