

H 6890 BP

Oven 90 cm

- the multi-talented expert from Miele.



- Multicoloured TFT touch display with clear text – M Touch
- Perfect baking and roasting results – Moisture plus
- Precise temperature control means cooking to perfection – wireless food probe
- Achieve perfect results with ease – automatic programmes
- Minimal cleaning effort – Pyrolytic cleaning

EAN: 4002515321744 / Material number: 09524000 / Old Material Number: 22689053GB

Construction type and design	
Built-in oven	•
Colour	Stainless steel/Clean Steel
PureLine	•
Convenience features	
Rapid heat-up	•
Food probe	Without cable
Crisp function	•
Rotisserie motor	•
Operating modes	
Defrosting	•
Country-specific automatic programmes	•
Auto roast	•
Eco hot air	•
Grill	•
Economy grill	•
Fan plus	•
Intensive bake	•
Moisture plus	•
Low temperature cooking	•
Conventional heat	•
Top heat	•
Bottom heat	•
Fan grill	•
Special applications	•
User convenience	
Networking with Miele@home	•
Display	M Touch
MultiLingua	•
MyMiele	•
3D control panel	•
Programmable timed steam injection	•
Polyphonic buzzers	•
Time of day display	•
Date display	•
Minute minder	•
Programmable cooking duration	•
Actual temperature display	•
Buzzer when desired temperature is reached	•
Recommended temperature	•
User programmes	•
Sabbath programme	•
Individual settings	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	A
Automatic residual heat utilisation	•
Cleaning and care	
Stainless steel/CleanSteel finish	•
Pyrolytic self-cleaning	•
Catalyser	•

H 6890 BP

Oven 90 cm

- the multi-talented expert from Miele.




EAN: 4002515321744 / Material number: 09524000 / Old Material Number: 22689053GB

Hinged grill element	•
CleanGlass door	•
Safety	
Appliance cooling system and touch-cool front	•
Safety switch-off	•
System lock	•
Door lock during pyrolytic cleaning	•
Technical data	
Oven compartment volume in l	90
No. of shelf levels	3
Number of shelf levels oven compartment 1	3
Number of shelf levels oven compartment 2	3
Numbered shelf levels	•
TwinPower hot air fan	•
Niche width min. in mm	860
Niche width max. in mm	860
Niche height min. in mm	517
Niche height max. in mm	517
Niche depth in mm	550
Appliance width in mm	848
Appliance height in mm	474
Appliance depth in mm	546
Weight in kg	74,0
Total rated load in kW	5,60
Voltage in V	230
Frequency in Hz	50
Fuse rating in A	25
Number of phases	1
Mains cable	•
Length of supply lead in m	1,75

H 6890 BP


Oven 90 cm

- the multi-talented expert from Miele.




HAL5900 (Installation drawing)

* Appliances with glass front, ** Appliances with metal front




HAL5900 (Installation drawing)

* Appliances with glass front, ** Appliances with metal front



H 5981 BP, H 6890 BP - 90 cm (Installation drawing)

* Appliances with glass front, ** Appliances with metal front



H 5981 BP, H 6890 BP - 90 cm (Installation drawing)

* Appliances with glass front, ** Appliances with metal front