

DG 6200

Built-in steam oven

with discreet display and integrated sensors for easy operation.



- Perfect results thanks to MultiSteam technology
- Simultaneous cooking on 3 levels without flavour transfer
- Very versatile and efficient thanks to extra large tray size
- Success guaranteed – intelligent automatic programmes
- Easy cleaning with flush control panel

EAN: 4002515286395 / Material number: 09538680 / Old Material Number: 23620050GB

Construction type and design	
Built-in steam oven	•
Colour	Stainless steel/Clean Steel
PureLine	•
Convenience features	
External steam generation	•
Menu cooking without transfer of taste	•
Automatic programmes with ability to make individual adjustments	•
Operating modes	
Steam cooking	•
User convenience	
Display	EasySensor
Quantity-independent cooking	•
Steam cooking on up to 3 levels at the same time	•
Steam reduction before end of programme	•
Actual temperature display	•
Buzzer when desired temperature is reached	•
Individual settings	•
Cleaning and care	
Stainless steel/CleanSteel finish	•
Stainless steel oven compartment	•
External steam generator	•
Floor heater for condensate reduction	•
Quick-release side racks	•
Descaling	•
CleanGlass door	•
Steam techn./water supply	
DualSteam	•
Fresh water container volume in l	2,0
Safety	
Appliance cooling system and touch-cool front	•
Safety switch-off	•
Vapour cooling system	•
Technical data	
Oven compartment volume in l	38
No. of shelf levels	4
Door hinge	Bottom
Niche width min. in mm	560
Niche width max. in mm	568
Niche height min. in mm	450
Niche height max. in mm	452
Niche depth in mm	550
Appliance dimensions (W x H x D) in mm	595 x 456 x 572
Appliance width in mm	595
Appliance height in mm	456
Appliance depth in mm	572
Weight in kg	29,4
Total rated load in kW	3,60
Voltage in V	230

DG 6200

Built-in steam oven

with discreet display and integrated sensors for easy operation.




EAN: 4002515286395 / Material number: 09538680 / Old Material Number: 23620050GB

Frequency in Hz	50-60
Fuse rating in A	16
Number of phases	1
Mains cable	•
Length of supply lead in m	2
Accessories included	
No. of perforated stainless-steel cooking container	3
Wire rack	1
Drip tray DGG 100 40	1

DG 6200


Built-in steam oven

with discreet display and integrated sensors for easy operation.




DG 6000 in combination with H 6000 (Installation drawing)

* Appliances with glass front, ** Appliances with metal front



DG 6000 (Installation drawing)

* Appliances with glass front, ** Appliances with metal front



DG 6000 – detail drawing PureLine (Installation drawing)

* Appliances with glass front, ** Appliances with metal front