

U 876

Lower basket carrier

for inserts or baskets up to 50 x 50 cm.



- Suitable for holding plastic baskets


EAN: 4002515274996 / Material number: 09549160 / Old Material Number: 67187501D

| Product category | |
|--------------------------------|-----------------|
| Fresh-water dishwashers | • |
| Machine affiliation | |
| PG 8041 | • |
| PG 8043 | • |
| PG 8045 | • |
| PG 8055 | • |
| PG 8055 U | • |
| PG 8056 | • |
| PG 8056 U | • |
| PG 8057 TD | • |
| PG 8057 TD U | • |
| PG 8058 | • |
| PG 8058 U | • |
| PG 8059 | • |
| PG 8059 U | • |
| PG 8060 | • |
| PG 8061 | • |
| PG 8061 U | • |
| PG 8096 | • |
| PG 8096 U | • |
| PG 8099 | • |
| PG 8099 U | • |
| PFD 400 | • |
| PFD 400 U | • |
| PFD 401 | • |
| PFD 401 U | • |
| PFD 402 | • |
| PFD 402 U | • |
| PFD 404 | • |
| PFD 404 U | • |
| PFD 405 | • |
| PFD 405 U | • |
| PFD 407 | • |
| PFD 407 U | • |
| PFD 408 U | • |
| Product category | |
| Carrier/basket carrier | • |
| Carrier | • |
| Lower basket carrier | • |
| Product properties | |
| Material | Stainless steel |
| Colour | Stainless Steel |
| Standard electrical connection | |
| Number of phases | 0 |
| Voltage in V | 0 |
| Frequency in Hz | 0 |
| Total rated load in kW | 0,00 |
| Fuse rating in A | 0 |

U 876

Lower basket carrier

for inserts or baskets up to 50 x 50 cm.



EAN: 4002515274996 / Material number: 09549160 / Old Material Number: 67187501D

| Dimensions and weight | |
|---|------|
| External dimensions, net height in mm | 50 |
| External dimensions, net width in mm | 535 |
| External dimensions, net depth in mm | 500 |
| External dimensions, gross height in mm | 530 |
| External dimensions, gross width in mm | 285 |
| External dimensions, gross depth in mm | 530 |
| Net weight in kg | 2,97 |
| Gross weight in kg | 3,12 |