

KS 37472 iD

Built-in refrigerator

PerfectFresh and FlexiLight for best storage conditions and high convenience.



- Food stays fresh for longer – PerfectFresh
- Individually adjustable glass shelf lighting thanks to FlexiLight
- Store food anywhere in the refrigerator – DynaCool
- Door shelves can be cleaned in the dishwasher – ComfortClean
- Soft-closing doors thanks to SoftClose

EAN: 4002515382417 / Material number: 09728810 / Old Material Number: 36374722AUS

Appliance category	
Refrigerator	•
Construction type	
Built-in appliance	•
Integrated appliance	•
Door hinge	right
Convertible door hinging	•
Side-by-side enabled	•
Design	
Refrigeration section lighting	FlexiLight
User convenience	
Networking with Miele@home	•
Accessories required	XKS 3130 W, XKV 3000 KF
Freshness system	PerfectFresh
ComfortClean	•
DynaCool	•
SoftClose	•
SelfClose	•
Controls	
Operating concept	TouchControl
Fridge compartment can be switched off	No
Independent temperature regulation of fridge and freezer zones	No
Automatic SuperCool	•
No. of temperature zones	2
Sabbath mode	•
Fridge/Fridge section	
No. of shelves	6
of which illuminated	4
Chrome-plated metal bottle rack	•
No. of crisper drawers	3
Number of inner door racks for tinned food	3
Door rack for bottles	2
Door shelves	5
Safety	
Lock function	•
Acoustic door alarm	•
Optical door alarm	•
Technical data	
Niche width in mm min.	560
Niche width in mm max.	570
Niche height in mm min.	1772
Niche height in mm max.	1788
Niche depth in mm	550
Appliance width in mm	559
Appliance height in mm	1770
Appliance depth in mm	544
Weight in kg	71,7
Door hinge technology	Fixed door
Max. door front weight – refrigerator, in kg	26

KS 37472 iD

Built-in refrigerator

PerfectFresh and FlexiLight for best storage conditions and high convenience.




EAN: 4002515382417 / Material number: 09728810 / Old Material Number: 36374722AUS

Climate class	SN-T
including PerfectFresh zone in l	92
Total usable capacity in l	308
Storage time in case of fault in h	0
Current consumption (mA)	1200
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2,1
Replacing lamps	Customer Service
Accessories supplied	
Butter dish	•
Egg tray	•

KS 37472 iD

Built-in refrigerator

PerfectFresh and FlexiLight for best storage conditions and high convenience.



K37422iD,K37222iDf,K37442iDf,K37473iD,K37282iDf,K37682iDf, K37683iDf, K37272iD, K37472iD, KS37422iD, FN37402i, FNS37402i