

DA 3466

Slimline cooker hood

with LED lighting and push-button controls for convenient operation.



- Elegant design – slim 595 mm extractor canopy
- Powerful – 550 m³/h in Booster level
- Efficient filtration- 10-ply stainless-steel grease filter
- Safe and easy to clean – Miele CleanCover
- Suitable for every home – for extraction or recirculation

EAN: 4002515520192 / Material number: 09884060 /
Old Material Number: 28346655D

General information	
Model identifier	DA 3466
Manufacturer material number	09884060
EAN number	4002515520192
Marketing class	Gold
Construction type	
Slimline cooker hood	•
Construction type and design	
Colour	Stainless steel
Operating modes	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUU 151
Active charcoal filter (order separately)	DKF 13-P
User convenience	
Electronic controls	•
Power levels (number without Booster level)	3
Booster levels	1
Easy-to-clean canopy interior – CleanCover	•
Efficiency	
Energy efficiency class (A+++ – D)	B
Annual energy consumption in kWh/year	69,5
Fluid dynamic efficiency class	C
Lighting efficiency class	A
Grease filtering efficiency class	B
Filter system	
Number of dishwasher-safe stainless steel grease filters (10-ply)	1
Lighting	
Number x W	2 x 3 W
Light intensity in lx	320 lx
Colour temperature in K	3000 Kelvin
Fan	
Dual-action fan	•
Exhaust air	
Air throughput in Level 1 (m ³ /h) according to EN 61591	150
Air throughput in Level 2 (m ³ /h) according to EN 61591	275
Air throughput in Level 3 (m ³ /h) according to EN 61591	400
Air throughput in Booster level 1 (m ³ /h) according to EN 61591	550
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	45,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	51,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	56,0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	64,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	32,0

DA 3466

Slimline cooker hood

with LED lighting and push-button controls for convenient operation.



EAN: 4002515520192 / Material number: 09884060 /

Old Material Number: 28346655D

Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	39,0
--	------

Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	44,0
--	------

Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	52,0
---	------

Recirculation

Air throughput in Level 1 (m³/h) according to EN 61591	80
--	----

Air throughput in Level 2 (m³/h) according to EN 61591	180
--	-----

Air throughput in Level 3 (m³/h) according to EN 61591	280
--	-----

Air throughput in Booster level 1 (m³/h) according to EN 61591	350
--	-----

Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	53,0
--	------

Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	61,0
--	------

Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	67,0
--	------

Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	72,0
---	------

Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	40,0
--	------

Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	48,0
--	------

Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	54,0
--	------

Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	60,0
---	------

Safety

Safety switch-off	•
-------------------	---

Technical data

Canopy width in in. (mm)	595
--------------------------	-----

Canopy height in in. (mm)	34
---------------------------	----

Net weight in kg	12,0
------------------	------

Depth of hood canopy in in. (mm)	275
----------------------------------	-----

Length of supply lead in m	1,5
----------------------------	-----

Standard plug fitted	•
----------------------	---

Minimum height above electric hobs in mm	450
--	-----

Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
--	-----

Total rated load in kW	0,18
------------------------	------

Voltage in V	230
--------------	-----

Fuse rating in A	10
------------------	----

Number of phases	1
------------------	---

Frequency in Hz	50
-----------------	----

Installation notes


Extraction ducting connection at top	•
--------------------------------------	---

Diameter of exhaust duct in mm	150
--------------------------------	-----

DA 3466

Slimline cooker hood

with LED lighting and push-button controls for convenient operation.



DA 3460, DA 3466 (installation drawing)

1) Der Oberschrank muss im vorderen Bereich bis zur Zwischenwand über einen Unterboden verfügen. Wird das Gerät weiter hinten montiert, z.B. bei Montage einer Frontblende, muss auch der Unterboden entsprechend tiefer sein., 2) Die Zwischenwand des Oberschranks muss herausnehmbar sein., 3) Abluft; bei Maßen für Schrankhöhe und Ausschnitte ist montiertes Zubehör zu berücksichtigen (z.B. Schalldämpfer, DSM-Modul), , 4) Umluft mit Umbausatz DUU 151, 5) Zubehör DSM 400, , 6) Bei Montage mit Absenkrahmen DAR 3000: Abweichende Schrankhöhe beachten (siehe Maßskizze DAR 3000)