

PG 8592 [WW AD]  
Washer-disinfector  
with liquid dispensing & hot air drying DryPlus.



- Performance/cycle, e.g. 8 DIN mesh trays or 1-2 MIS sets
- Safety through monitoring – wash pressure and spray arm monitoring
- 68 % less water consumption compared to predecessor model\*
- Efficient hot air drying – DryPlus
- Total security – link to process documentation possible

\* compared to VarioTD programme for G 7892

EAN: 4002515628805 / Material number: 10221090 / Old Material Number: 62859201AE

<b>Construction type and version</b>	
Construction type	Freestanding, can be built-under, slimline
Casing	Stainless steel
Can be built-under	•
AutoClose – automatic door lock	•
Buzzer, acoustic signal at end of programme	•
Service-friendly design	•
<b>Application</b>	
Suitable for hospitals	•
Suitable for doctors' surgeries	•
Suitable for outpatient surgeries	•
Suitable for fire brigades and rescue services	•
<b>Capacity</b>	
DIN mesh trays per cycle [number]	8
GYN specula per cycle [number]	42
MIS sets per cycle [number]	1-2
AN sets per cycle [number]	2-3
Lumened instruments per cycle [number]	44
<b>Performance data</b>	
Circulation pump, Qmax in l/min	500
Wash cabinet usable capacity in l	145,00
Tested operating hours	15000
Shortest programme running time (cleaning and disinfection) in min	22
Maximum final rinse temperature in °C	93
<b>Control system</b>	
Control type	TouchControl
Programme selection	Touch on MSetal
Direct-access pushbuttons	•
Max. delay start in h	24
Programmability	programmable
Programmes [number]	19
Free programme positions [number]	2
A0 value controls	•
Automatic programme restart	•
Time left display	•
Programme sequence display	•
Selectable display languages	•
<b>Standard electrical connection</b>	
Electrical connection	3N AC 400V 50HZ
Electric heater rating in kW	8,50
Total rated load in kW	9,30
Fuse rating in A	16
Length of mains connection cable in m	1,80
<b>Possible voltage variant 1</b>	
Electrical connection	AC 230V 50HZ
Electric heater rating in kW	2,50
Total rated load in kW	3,30
Fuse rating in A	16

PG 8592 [WW AD]  
Washer-disinfector  
with liquid dispensing & hot air drying DryPlus.



EAN: 4002515628805 / Material number: 10221090 / Old Material Number: 62859201AE

Water connection/drainage	
Cold water [number]	1
Cold water for steam condenser [number]	1
Hot water [number]	1
Required flow pressure in kPa	200-1000
DI water [number]	1
Maximum delivery head for drain pump in cm	100
Maximum water hardness (cold water/hot water) in mmol/l	10,70
Drain pump [DN]	22
Integrated water softener	•
Water protection system	Waterproof system
Dimensions and weight	
External dimensions, net height in mm	820
External dimensions, net width in mm	600
External dimensions, net depth in mm	600
Wash cabinet, usable height in mm	520
Wash cabinet, usable width in mm	530
Net weight in kg	78
Drying unit	
Integrated drying unit	•
Fan in kW	0,30
Heater element in kW	2,20
Air throughput in m <sup>3</sup> /h	60
Time setting in 1-minute increments	0-120
HEPA filter class	H13
HEPA filter filtration efficiency (in accordance with DIN EN 1822) in %	99,95
Dimensions and weight	
External dimensions, gross height in mm	940
External dimensions, gross width in mm	675
External dimensions, gross depth in mm	745
Wash cabinet, depth of upper basket in mm	474
Wash cabinet, depth of lower basket in mm	520
Gross weight in kg	85
Emissions data	
Emission sound pressure level in the workplace	<70 dB(A) re 20 µPa
Heat dissipation into the room in MJ/h	1,45
Features	
Volume flow control	•
Interface for process documentation (optional)	•
Customer Service interface	•
Extensive components (option)	•
Programmes	
Vario TD Instr 4 mesh trays	•
Vario TD Instr 6 mesh trays	•
Vario TD Instr 8 mesh trays	•
Vario TD AN	•
Vario TD MIS	•
Vario TD GYN	•
Vario TD ENT	•
Vario TD ENT +	•
Vario TD ENT Optics	•

PG 8592 [WW AD]  
Washer-disinfector  
with liquid dispensing & hot air drying DryPlus.