


ESW 6229 X

29 cm high handleless Gourmet warming drawer

with the low temperature cooking function - much more than a warming drawer.



- Ultimate enjoyment with Low temperature cooking
- Versatile use thanks to four operating modes
- Convenient and easy – Touch control
- Easiest handling – Push2Open
- Safe is safe – Timer function with automatic switch off


EAN: 4002515751817 / Material number: 10456440 / Old Material Number: 30622964GB

Construction type and design	
Gourmet warming drawer	•
PureLine	•
ArtLine	•
ContourLine	•
Handleless	•
Colour	Graphite grey
Operating modes	
Cup warming	•
Plate warming	•
Keeping food warm	•
Low temperature cooking	•
User convenience	
Capacity	12 place settings
Push2open mechanism	•
Fully telescopic runners for easy loading and unloading of the warming drawer	•
Control panel with sensor controls	•
Control panel with symbols	•
Stop programming	•
Timer function	•
Cleaning and care	
Flush control panel	•
Safety	
Cool front	•
Anti-slip mat	•
Safety switch-off	•
Technical data	
Appliance width in mm	595
Appliance height in mm	289
Appliance depth in mm	570
Useable interior height in mm	230
Total rated load in kW	0,70
Voltage in V	230
Frequency in Hz	50-60
Fuse rating in A	10
Number of phases	1
Mains cable with plug	•
Length of supply lead in m	2,0
Accessories included	
Anti-slip mat	1
Rack for increased capacity	1

ESW 6229 X


29 cm high handleless Gourmet warming drawer

with the low temperature cooking function - much more than a warming drawer.




ESW 6129, ESW 6229 CLST (Installation drawing)

* Appliances with glass front, ** Appliances with metal front




ESW 6129, ESW 6229 CLST (Installation drawing)

* Appliances with glass front, ** Appliances with metal front




ESW 6129, ESW 6229 CLST (Installation drawing)

* Appliances with glass front, ** Appliances with metal front




ESW 6129, ESW 6229 CLST (Installation drawing)

* Appliances with glass front, ** Appliances with metal front




ESW 6129, ESW 6229 CLST (Installation drawing)

* Appliances with glass front, ** Appliances with metal front



ESW 6129, ESW 6229 (Installation drawing)

* Appliances with glass front, ** Appliances with metal front



ESW 6129 X, ESW 6229 X (Installation drawing) – handleless

* Appliances with glass front, ** Appliances with metal front