

H 6860 BPX

Handleless oven

- the multi-talented expert from Miele.



- handleless kitchen design and convenient door opening – Touch2Open
- Multicoloured TFT touch display with clear text – M Touch
- Perfect baking and roasting results – Moisture plus
- Precise temperature control means cooking to perfection – wireless food probe
- Achieve perfect results with ease – automatic programmes

EAN: 4002515757680 / Material number: 10461030 /

Old Material Number: 22686061GB

Construction type and design	
ArtLine	•
Handleless	•
Construction type and design	
Built-in oven	•
Convenience features	
Rapid heat-up	•
Food probe	Without cable
Crisp function	•
Operating modes	
Fan plus	•
Conventional heat	•
Moisture plus	•
Intensive bake	•
Auto roast	•
Fan grill	•
Grill	•
Economy grill	•
Top heat	•
Bottom heat	•
Low temperature cooking	•
Eco hot air	•
Defrosting	•
Country-specific automatic programmes	•
Special applications	•
Design	
Colour	Brilliant white
User convenience	
Networking with Miele@home	•
Display	M Touch
SoftOpen	•
Touch2Open	•
MultiLingua	•
MyMiele	•
Programmable timed steam injection	•
Polyphonic buzzers	•
Time of day display	•
Date display	•
Minute minder	•
Programmable cooking duration	•
Actual temperature display	•
Buzzer when desired temperature is reached	•
Recommended temperature	•
User programmes	•
Individual settings	•
Efficiency and sustainability	
Energy efficiency class (A+++ – D)	A+
Automatic residual heat utilisation	•

H 6860 BPX

Handleless oven

- the multi-talented expert from Miele.



EAN: 4002515757680 / Material number: 10461030 /

Old Material Number: 22686061GB

Cleaning and care

Pyrolytic self-cleaning

•

Catalyser

•

Hinged grill element

•

CleanGlass door

•

Safety

Appliance cooling system and touch-cool front

•

Safety switch-off

•

System lock

•

Door lock during pyrolytic cleaning

•

Technical data

Oven compartment volume in l

76

No. of shelf levels

5

Number of shelf levels oven compartment 1

5

Number of shelf levels oven compartment 2

5

Numbered shelf levels

•

Niche width min. in mm

560

Niche width max. in mm

568

Niche height min. in mm

593

Niche height max. in mm

595

Niche depth in mm

550

Appliance width in mm

554

Appliance height in mm

579

Appliance depth in mm

547

Weight in kg

47,0

Total rated load in kW

3,70

Voltage in V

230

Length of supply lead in m

1,70

Frequency in Hz

50

Fuse rating in A

16

Number of phases

1

Mains cable

•


Mains cable with plug

•

H 6860 BPX

Handleless oven

- the multi-talented expert from Miele.




H 5000 EP/BP – 60 cm (Installation drawing)

* Appliances with glass front, ** Appliances with metal front

H 5000 BP; H 6000 BP; H 2000 BP; 60 cm (Installation drawing)

* Appliances with glass front, ** Appliances with metal front



Detailed installation drawing H 6000 BPX, ArtLine, 76 Litres, (Installation drawing)