

A 208

Mobile unit

For the optimum loading of 8 mesh trays.



- High capacity: simultaneous reprocessing of 8 DIN mesh trays
- 4 additional connections for hollow instruments
- Removable level increases vertical clearance if required

EAN: 4002515809242 / Material number: 10616030 / Old Material Number: 69620800D

|   |                          |
|---|--------------------------|
| <b>Product category</b>                 |                          |
| Washer-disinfectors, medical            | •                        |
| <b>Machine affiliation</b>              |                          |
| PG 8582                                 | •                        |
| PG 8582 CD                              | •                        |
| PG 8592                                 | •                        |
| <b>Product category</b>                 |                          |
| Mobile unit for mesh trays              | •                        |
| <b>Product properties</b>               |                          |
| Material                                | Stainless steel, Plastic |
| Colour                                  | Stainless Steel, Black   |
| <b>Area of application</b>              |                          |
| Reprocessing of mesh trays              | •                        |
| <b>Capacity</b>                         |                          |
| DIN mesh trays [number]                 | 8                        |
| Lumened instruments [number]            | 4                        |
| <b>Standard electrical connection</b>   |                          |
| Number of phases                        | 0                        |
| Voltage in V                            | 0                        |
| Frequency in Hz                         | 0                        |
| Total rated load in kW                  | 0,00                     |
| Fuse rating in A                        | 0                        |
| <b>Dimensions and weight</b>            |                          |
| External dimensions, net height in mm   | 397                      |
| External dimensions, net width in mm    | 529                      |
| External dimensions, net depth in mm    | 546                      |
| External dimensions, gross height in mm | 270                      |
| External dimensions, gross width in mm  | 525                      |
| External dimensions, gross depth in mm  | 540                      |
| Net weight in kg                        | 4,40                     |
| Gross weight in kg                      | 6,40                     |