

KFN 15842 D edt/cs
Freestanding fridge-freezer
75 cm wide for plenty of storage space.



- Optimum and maintenance-free LED lighting in compartment
- High efficiency and top-class freshness
- No icing up of food and no need to defrost thanks to Frost free
- Convenient and effortless opening – EasyOpen

EAN: 4002515887523 / Material number: 10721480 / Old Material Number: 38158420EU1

Appliance category	
Fridge-freezer	•
Construction type	
Freestanding appliance	•
Door hinge	right
Convertible door hinging	•
Design	
Casing colour	Stainless steel look
Front colour	Stainless steel/CleanSteel
Refrigeration section lighting	LED
User convenience	
ComfortClean	•
DynaCool	•
NoFrost	•
DuplexCool	•
VarioRoom	•
SoftClose	•
Concealed door opener	EasyOpen lever handle
Control system	
Operating concept	TouchControl
Fridge compartment can be switched off	Yes
Independent temperature regulation of fridge and freezer zones	Yes
Automatic SuperCool	•
SuperFreeze	•
No. of temperature zones	2
Sabbath mode	•
Fridge/Fridge section	
No. of shelves	4
Chrome-plated metal bottle rack	•
of which on castors	2
Number of inner door racks for tinned food	4
Half-width door shelves	4
Door rack for bottles	1
Door shelves	5
Freezer/Freezer section	
Number of freezer drawers	2
Efficiency and sustainability	
Energy efficiency class (A–G)	F
Annual energy consumption in kWh	241,63
Energy consumption in 24 h in kWh	0,66
Safety	
Lock function	•
Acoustic door alarm	•
Acoustic temperature alarm	•
Optical door alarm	•
Optical temperature alarm	•
Power cut indication for freezer section	•
Technical data	
Niche width in mm min.	762


KFN 15842 D edt/cs
Freestanding fridge-freezer
75 cm wide for plenty of storage space.



EAN: 4002515887523 / Material number: 10721480 / Old Material Number: 38158420EU1

Niche width in mm max.	762
Niche height in mm min.	1873
Niche height in mm max.	1873
Niche depth in mm	610
Appliance width in mm	747
Appliance height in mm	1859
Appliance depth in mm	630
Weight in kg	104,0
Climate class	SN-T
Refrigerator compartment in l	332
4* freezer compartment in l	89
Total usable capacity in l	420
Storage time in case of fault in h	12
Freezer capacity in kg/24 h	10,00
Acoustic airborne noise emission class (A-D)	D
Sound emissions in dB(A) re 1 pW	42
Current consumption (mA)	1500
Voltage in V	220-240
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
Length of supply lead in m	2,4
Replacing lamps	Service
Accessories included	
Butter dish	•
Egg tray	•
Ice packs	•
Ice cube tray	•

KFN 15842 D edt/cs
Freestanding fridge-freezer
75 cm wide for plenty of storage space.



KFN14842SDed/cs-1 (installation drawings) (*footnote)

*To ensure that energy consumption as stated is achieved, machines should be used together with the enclosed spacer brackets. This increases the total depth of the unit by approx. 3.5 cm. , Machines are still fully functional when operated without these brackets but have a slightly higher energy consumption.,