

DOS G 80/1 Flex

Hose dispenser pump for 5 l containers

With level indicator for the automatic dispensing of liquid cleaning agents.

EAN: 4002516331605 / Material number: 10730810 / Old Material Number: 67747045D



- For canisters up to 202 mm tall (up to canister opening)
- Dispenses up to 55 Milliliter ml per minute
- Set via the dishwasher controls
- Flexible vent valve cap
- 214 mm mm siphon for 5 l media canisters

Product category	
Fresh-water dishwashers	•
Tank dishwashers	•
Washer-disinfectors, laboratory	•
Machine affiliation	
PG 8041	•
PG 8043	•
PG 8045	•
PG 8055	•
PG 8055 U	•
PG 8056	•
PG 8056 U	•
PG 8057 TD	•
PG 8057 TD U	•
PG 8058	•
PG 8058 U	•
PG 8059	•
PG 8059 U	•
PG 8060	•
PG 8063	•
PG 8096	•
PG 8096 U	•
PG 8099	•
PG 8099 U	•
PFD 400	•
PFD 400 U	•
PFD 401	•
PFD 401 U	•
PFD 402	•
PFD 402 U	•
PFD 404	•
PFD 404 U	•
PFD 405	•
PFD 405 U	•
PFD 407	•
PFD 407 U	•
Product category	
External dispensing system	•
Product properties	
Material	Plastic
Colour	Grey
Production rate in ml/60 s	55
Length of suction lance in mm	214
Length of dispensing hose to suction lance in mm	1800
Length of dispensing hose from machine to dispensing module in mm	2850
Length of mains connection cable to machine in mm	2800
Minimum width of canister opening in mm	31
Maximum width of canister opening in mm	60

DOS G 80/1 Flex

Hose dispenser pump for 5 l containers

With level indicator for the automatic dispensing of liquid cleaning agents.

EAN: 4002516331605 / Material number: 10730810 / Old Material Number: 67747045D



Standard electrical connection	
Number of phases	1
Neutral conductor	N
AC/DC	AC
Voltage in V	200-230
Frequency in Hz	50
Total rated load in kW	0,01
Fuse rating in A	0
Dimensions and weight	
External dimensions, net height in mm	114
External dimensions, net width in mm	115
External dimensions, net depth in mm	139
External dimensions, gross height in mm	160
External dimensions, gross width in mm	198
External dimensions, gross depth in mm	478
Net weight in kg	2,23
Gross weight in kg	2,49