

DOS G 80 ProfiLine Flex  
Hose metering pump  
with level indicator for the automatic dispensing of liquid cleaning agents.



- For canisters up to 340 mm tall (up to canister opening)
- Dispenses up to 55 Milliliter ml per minute
- Set via the dishwasher controls
- Flexible cap (covers DIN 50 and 51 threads)
- Min. canister opening: 31 mm

EAN: 4002516330608 / Material number: 10730840 / Old Material Number: 67747050D

<b>Product category</b>	
Fresh-water dishwashers	•
<b>Machine affiliation</b>	
PG 8080	•
PG 8080 i	•
PG 8080 U	•
PG 8080 U/i	•
PG 8081 i	•
PG 8082 SCi XXL	•
PG 8083 SCVi XXL	•
PG 8130	•
PG 8130 U	•
PG 8130 i	•
PG 8130 U/i	•
PG 8131 i	•
PG 8132 SCi	•
PG 8133 SCVi	•
PFD 100 (SmartBiz)	•
PFD 101	•
PFD 101 i	•
PFD 101 U	•
PFD 101 U/i	•
PFD 102 i	•
PFD 103 SCi XXL	•
PFD 104 SCVi XXL	•
<b>Product category</b>	
External dispensing system	•
<b>Product properties</b>	
Material	Plastic
Colour	Grey
Production rate in ml/60 s	55
Length of suction lance in mm	352
Length of dispensing hose to suction lance in mm	1800
Length of dispensing hose from machine to dispensing module in mm	2850
Length of mains connection cable to machine in mm	2800
Minimum width of canister opening in mm	31
Maximum width of canister opening in mm	60
<b>Standard electrical connection</b>	
Number of phases	1
Neutral conductor	N
AC/DC	AC
Voltage in V	200-230
Frequency in Hz	50
Total rated load in kW	0,01
<b>Dimensions and weight</b>	
External dimensions, net height in mm	114
External dimensions, net width in mm	115
External dimensions, net depth in mm	139
External dimensions, gross height in mm	200

## DOS G 80 ProfiLine Flex

### Hose metering pump

with level indicator for the automatic dispensing of liquid cleaning agents.

EAN: 4002516330608 / Material number: 10730840 / Old Material Number: 67747050D



External dimensions, gross width in mm	480
External dimensions, gross depth in mm	150
Net weight in kg	2,09
Gross weight in kg	2,29