

DA 4228 W Puristic Plus  
Wall mounted cooker hood  
with energy-efficient LED lighting and light-touch switches for easy use.



- Timeless design – stainless steel canopy 1198 mm wide
- Unique user convenience – Con@ctivity
- Powerful – 630 m<sup>3</sup>/h in Booster level
- Pleasantly quiet – Miele Silence package
- Safe and easy to clean – Miele CleanCover

EAN: 4002515935750 / Material number: 10749560 / Old Material Number: 28422850D

<b>Construction type</b>	
Wall mounted cooker hood	•
<b>Operating modes</b>	
Type of air guide	Exhaust air
<b>Design</b>	
Colour	Stainless steel
RAL colours available as customisation on request	•
Customisation possible on request	•
<b>User convenience</b>	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number without Booster level)	3
Miele@mobile app	•
Programmable Booster level switch-off	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Grease filter saturation indicator programmable	•
Silence package	•
Easy-to-clean canopy interior – CleanCover	•
<b>Efficiency and sustainability</b>	
Annual energy consumption in kWh/year	28,8
Energy efficiency class (A+++ – D)	A++
ECO motor	•
PowerManagement system	•
Annual energy consumption in kWh/year	28,8
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	A
<b>Filter system</b>	
Number of dishwasher-safe stainless steel grease filters (10-ply)	4
<b>Lighting</b>	
LED	•
Number x W	3 x 3 W
Light intensity in lx	440 lx
Colour temperature in K	3500 Kelvin
Dimmer function	•
<b>Fan</b>	
Dual-action fan	•
DC motor	•
<b>Exhaust air</b>	
Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591	190
Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591	290
Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591	390
Air throughput in Booster level (m <sup>3</sup> /h) according to EN 61591	630
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	36,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	45,0


DA 4228 W Puristic Plus  
Wall mounted cooker hood  
with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002515935750 / Material number: 10749560 / Old Material Number: 28422850D

Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	52,0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	64,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	21,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	30,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	37,0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	49,0
<b>Safety</b>	
Safety switch-off	•
<b>Technical data</b>	
Overall hood height for extraction mode and external in mm	685–1005
Overall height for vented and external in in. (mm)	685
Canopy width in mm	1198
Overall height for extraction mode and external mode cooker hoods in mm	1005
Canopy height in mm	62
Canopy depth in mm	500
Minimum height above electric hobs in mm	450
Net weight in kg	27,0
Length of supply lead in m	1,5
Standard plug fitted	•
Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Total rated load in kW	0,08
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
<b>Installation notes</b>	
Extraction ducting connection at top	•
Extraction connection at top and rear	•
Diameter of exhaust duct in mm	150
Telescopic chimney	•
Combination with WiFi-enabled Miele hob	recommended
<b>Accessories included</b>	
Adapter to reduce ducting diameter from 150 mm to 125 mm Ø	•
Non-return flap	•
<b>Optional accessories</b>	
Active charcoal filter	Nein

DA 4228 W Puristic Plus  
Wall mounted cooker hood  
with energy-efficient LED lighting and light-touch switches for easy use.



DA 4228 (Installation drawing)  
1) and 2) Installation cut-out