

DA 4208 D Puristic Plus  
Island cooker hood  
with energy-efficient LED lighting and light-touch switches for easy use.



- Timeless design – stainless steel canopy 898 mm wide
- Unique user convenience – Con@ctivity
- Powerful – 720 m<sup>3</sup>/h in Booster level
- Pleasantly quiet – Miele Silence package
- Suitable for every home – for extraction or recirculation

EAN: 4002515937808 / Material number: 10767240 / Old Material Number: 28420850D

<b>Construction type</b>	
Island cooker hood	•
<b>Operating modes</b>	
Type of air guide	Can be retrofitted
Recirculation conversion kit (order separately)	DUI 32
Active charcoal filter (order separately)	DKF 12-P
<b>Design</b>	
Colour	Stainless steel
RAL colours available as customisation on request	•
Customisation possible on request	•
<b>User convenience</b>	
Miele@home	•
Automatic function Con@ctivity	•
Electronic controls	•
Power levels (number without Booster level)	3
Miele@mobile app	•
Programmable Booster level switch-off	•
Run-on time 5/15 min.	•
Grease filter saturation indicator	•
Grease filter saturation indicator programmable	•
Active charcoal filter saturation indicator programmable	•
Silence package	•
Easy-to-clean canopy interior – CleanCover	•
<b>Efficiency and sustainability</b>	
Annual energy consumption in kWh/year	29,9
Energy efficiency class (A+++ – D)	A++
Fluid dynamic efficiency class	A
Lighting efficiency class	A
ECO motor	•
Grease filtering efficiency class	A
PowerManagement system	•
Annual energy consumption in kWh/year	29,9
Fluid dynamic efficiency class	A
Lighting efficiency class	A
Grease filtering efficiency class	A
<b>Filter system</b>	
Number of dishwasher-safe stainless steel grease filters (10-ply)	3
<b>Lighting</b>	
LED	•
Number x W	4 x 3 W
Light intensity in lx	820 lx
Colour temperature in K	3500 Kelvin
Dimmer function	•
<b>Fan</b>	
Dual-action fan	•
DC motor	•
<b>Exhaust air</b>	
Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591	200
Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591	320

DA 4208 D Puristic Plus  
Island cooker hood  
with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002515937808 / Material number: 10767240 / Old Material Number: 28420850D

Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591	450
Air throughput in Booster level (m <sup>3</sup> /h) according to EN 61591	720
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	36,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	45,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	54,0
Sound power in Booster level (dB(A) re 1 pW) acc. to EN 60704-3	65,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	21,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	30,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	39,0
Sound pressure in Booster level (dB(A) re 20 µPa) acc. to EN 60704-2-13	50,0
<b>Recirculation</b>	
Air throughput in Level 1 (m <sup>3</sup> /h) according to EN 61591	110
Air throughput in Level 2 (m <sup>3</sup> /h) according to EN 61591	190
Air throughput in Level 3 (m <sup>3</sup> /h) according to EN 61591	320
Air throughput in Booster level 1 (m <sup>3</sup> /h) according to EN 61591	480
Sound power in Level 1 (dB(A) re 1 pW) according to EN 60704-3	47,0
Sound power in Level 2 (dB(A) re 1 pW) according to EN 60704-3	56,0
Sound power in Level 3 (dB(A) re 1 pW) according to EN 60704-3	64,0
Sound power in Booster level 1 (dB(A) re 1 pW) acc. to EN 60704-3	73,0
Sound pressure in Level 1 (dB(A) re 20 µPa) according to EN 60704-2-13	32,0
Sound pressure in Level 2 (dB(A) re 20 µPa) according to EN 60704-2-13	41,0
Sound pressure in Level 3 (dB(A) re 20 µPa) according to EN 60704-2-13	49,0
Sound pressure in Booster level 1 (dB(A) re 20 µPa) acc. to EN 60704-2-13	57,0
<b>Safety</b>	
Safety switch-off	•
<b>Technical data</b>	
Overall height for vented and external in in. (mm)	690
Canopy width in mm	898
Overall height for extraction mode and external mode cooker hoods in mm	990
Canopy height in mm	70
Overall height for recirculation in in. (mm)	750
Canopy depth in mm	598
Overall height for recirculation mode cooker hoods in mm	1060
Minimum height above electric hobs in mm	450
Net weight in kg	34,0

## DA 4208 D Puristic Plus

### Island cooker hood


with energy-efficient LED lighting and light-touch switches for easy use.



EAN: 4002515937808 / Material number: 10767240 / Old Material Number: 28420850D


Hard-wired connection	•
Minimum safety distance above gas hobs (max. 12.6 kW total power, burner ≤ 4.5 kW) in mm	650
Total rated load in kW	0,11
Voltage in V	230
Fuse rating in A	10
Number of phases	1
Frequency in Hz	50
<b>Installation notes</b>	
Extraction ducting connection at top	•
Diameter of exhaust duct in mm	150
Telescopic chimney	•
Combination with WiFi-enabled Miele hob	recommended
<b>Accessories included</b>	
Non-return flap	•
<b>Optional accessories</b>	
Active charcoal filter	Nein
Active charcoal filter, can be reactivated	DKF 12-R

DA 4208 D Puristic Plus  
Island cooker hood  
with energy-efficient LED lighting and light-touch switches for easy use.



DA 410-6, DA 4208 D, DA 4208 D EXTA, DA 6396 D, DA 6596 D, PUR 98 D (Installation drawing)

1) Installation area/site, 2) Vented, 3) Recirculation, 4) Installation alternatively with spacer frame, 5) Ventilation grille positioned at the top for recirculation, 6) A supply lead, and for vented mode flexible vent ducting, must be pre-fitted for the connection in the ceiling to the connection of the cooker hood.



DA 420 V-6, DA 4208 VD (Installation drawing)

1) Installation area/site, 2) Vented, 3) Recirculation, 4) Installation alternatively with spacer frame, 5) Ventilation grille positioned at the top for recirculation, 6) A supply lead, and for vented mode flexible vent ducting, must be pre-fitted for the connection in the ceiling to the connection of the cooker hood.